


Barrier Strip

14.3mm Pitch

multicomp PRO


**RoHS
Compliant**



Specifications:

Current rating	: 30 Amp AC300V
Insulation withstands Volt	: AC2,000V min
Insulation resistance	: >2,000MΩ DC500V
Operation temperature	: -40°C to +120°C
Wire range	: 10AWG to 22AWG
Screw torque	: 14lb-inch

PCB Layout



Dimensions : Millimetres

Pitch : 14.3mm (0.563")			
Pole	L	S	Part Number
4	82.7mm	71.6	MC24342
6	111.3mm	100.2	MC24343
8	139.9mm	128.8	MC24344
10	168.5mm	157.4	MC24345
12	197.1	186	MC24346

Part Number Table

No.	Material	Plating/Finish	Remark
1	Insulating body	PBT	Black
2	Terminal	Brass	Tin plated
3	Screw	Steel	Zinc + Cr ⁺³

Description	Part Number
Barrier Strip, 14.3mm Pitch	MC24342
	MC24343
	MC24344
	MC24345
	MC24346

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO