

2108-BT/TV2M



2188RFI-2M



2189RFI-2M



Specification:

Current rating : 13A, 250V ac.

Construction:

Description	Material
Socket base and cover	ABS.
Socket terminals (bus bar)	Brass, phosphorus bronze.
Cover screw	Mild steel nickel plated.
Cord grip screw	
Terminal screw	Brass.
Switch	Nylon house with brass (nickel plated) terminals.
Cord grip	Nylon (PA).
Shutter	
Spring	Mild steel.
Neon lamp with 220k Ω resistor	Orange light.
Neon lamp cover	Polycarbonate (PC).
Switch rocker	
Plug	13A BS 1363 plug.
Cable	PVC, BS6500 3 x 1.25mm ² .

Approval:

Plug : BSI kitemark licence KM54406.

Standard:

BS 1363/A.

Conditions of Use:

- An ambient temperature in the range -5°C to +40°C, the average value over 24 hours not exceeding 25°C.
- A situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits.
- An altitude not exceeding 2000 metres above sea level; an atmosphere no subject to abnormal pollution by smoke, chemical fumes, rain, spray, prolonged periods of high humidity or other abnormal conditions.

Safety Specifications:

Item	Conditions	Requirements
Appearance	-	No defect such as cracks, deep scratches or blemishes.
Marking	-	Shall be legible and must be clear.
Insulation resistance	500 + 250V dc for 1 minute.	Shall not be less than 5MΩ.
Dielectric strength	2000 ±60V for 1 minute.	No damage or breakdown.
Resistance to aging	70° ±5° (168 hours).	No cracks or become sticky.
Construction	20° ±5°.	Complied with Figure 11, 12, 14 and 16 gauge.
Torque test	Value of 0.6Nm (6.1kgf/cm).	Terminal, cord grip and cover screws shall withstand the torque applied.
Glow wire test	650°/750° electrically heated.	Flame must extinguish within 30 seconds.
Temperature rise	14A, 250V.	Temperature rise must not exceed: 1. Terminals or terminations : 52K. 2. Accessible surface : 52K.
Make and break test of switch	13A, 250V (15,000 times)	Voltage drop across each switched pole shall not exceed 75mV.
Cord anchorage test	1. 3kg. Pull force test for 0.5mm ² cable. 2. 6kg. Pull force test for 1.0 mm ² or above cable.	The flexible cord shall not be displaced by more than 2mm after being pull 25 times.
Drop test	Fit with 3G1.25mm ² cable, 2.25m and drop at a height of 0.4m above the floor.	No external damage which might affect safety and no components shall have become detached.
Live parts accessibility	Subjected to 1.0mm test probe with applied force of 5N when they are mounted and wired as in normal use.	Live parts of socket shall not be accessible.

Specification Table

Description	Type	Part Number
Extension Lead, 3 Gang, Switched, 2M	Rewireable	2188RFI-2M
Extension Lead, 6 Gang, Switched, 2M		2189RFI-2M
		2108-BT/TV2M

Notes:

International Sales Offices:

	AUSTRALIA – Farnell Tel No: ++61 1300 361 005 Fax No: ++61 1300 361 225		FINLAND – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ITALY – Farnell Tel No: ++ 39 02 93 995 200 Fax No: ++ 39 02 93 995 300		SPAIN – Farnell Tel No: 901 20 20 80 Fax No: 901 20 20 90
	AUSTRIA – Farnell Tel No: ++ 43 662 2180 680 Fax No: ++ 43 662 2180 670		FRANCE – Farnell Tel No: ++ 33 474 68 99 99 Fax No: ++ 33 474 68 99 90		MALAYSIA – Farnell-Newark Tel No: ++ 60 3 7873 8000 Fax No: ++ 60 3 7873 7000		SWEDEN – Farnell Tel No: ++ 46 8 730 50 00 Fax No: ++ 46 8 83 52 62
	BELGIUM – Farnell Tel No: ++ 32 3 475 2810 Fax No: ++ 32 3 227 3648		GERMANY – Farnell Tel No: ++ 49 89 61 39 39 39 Fax No: ++ 49 89 613 59 01		NETHERLANDS – Farnell Tel No: ++ 31 30 241 7373 Fax No: ++ 31 30 241 7333		SWITZERLAND – Farnell Tel No: ++ 44 204 64 64 Fax No: ++ 44 204 64 54
	BRAZIL – Farnell-Newark Tel No: ++ 55 11 4066 9400 Fax No: ++ 55 11 4066 9410		HONG KONG – Farnell-Newark Tel No: ++ 852 2268 9888 Fax No: ++ 852 2268 9899		NEW ZEALAND – Farnell Tel No: 0800 90 80 80 Fax No: 0800 90 80 81		UK – Farnell Tel No: ++ 44 8701 200 200 Fax No: ++ 44 8701 200 201
	CHINA – Farnell-Newark Tel No: ++86 10 6238 5152 Fax No: ++86 10 6238 5022		HUNGARY - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		NORWAY – Farnell Tel No: 800 146 70 Fax No: 800 146 76		UK – CPC ++ 44 8701 202 530 ++ 44 8701 202 531
	CZECH REPUBLIC - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		INDIA - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		PORTUGAL – Farnell Tel No: ++ 34 93 475 8804 Fax No: ++ 34 93 474 5288		USA – Newark Tel No: 800 463 9275
	DENMARK – Farnell Tel No: ++ 45 44 53 66 44 Fax No: ++ 45 44 53 66 06		IRELAND – Farnell Tel No: ++ 353 1 830 9277 Fax No: ++ 353 1 830 9016		RUSSIA – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 EXPORT – Farnell Tel No: ++ 44 8701 200 208 Fax No: ++ 44 8701 200 209 For enquiries from all other markets	
	ESTONIA – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ISRAEL – Farnell Tel No: ++ 180 937 0015 Fax No: ++ 180 937 0014		SINGAPORE – Farnell-Newark Tel No: ++ 65 6788 0200 Fax No: ++ 65 6788 0300	http://www.farnell.com http://www.newark.com http://www.cpc.co.uk	

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Elec is the registered trademark of the Group. © Premier Farnell plc 2009.