Data Sheet

Coaxial Cable Connector 11_BNC-75-4-6/133_N

Description

Straight cable plug

Interface standards Interface compatible with IEC 61169-8

Technical Data

Electrical Data

Impedance Interface frequency max. Frequency range Return loss	75 Ω 1 GHz DC to 1 GHz 21 dB
Mechanical Data Centre contact Outer contact Weight	crimped crimped 0.0103 kg
Environmental Data Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing Catalogue drawing Assembly instruction	DOU-00071552 DCA-00198325 DOC-0000179061	
Ordering Information		
Bulk 100 pcs package Single package	11_BNC-75-4-6/133_NH 11_BNC-75-4-6/133_NE	
Additional Information		

Suitable cables

G_04233_D

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.



