

CAS SMD SFTY 250, Ceramic, 56 pF, 2%, COG, Industrial Grade, Safety MLCC, X1/Y2, 2211



**Dimensions**

Dimensions	
Chip Size	2211
L	5.7mm +/-0.4mm
W	2.8mm +/-0.3mm
T	2mm +/-0.2mm
S	4mm MIN
B	0.6mm +/-0.3mm

**Packaging Specifications**

Packaging:	T&R
Packaging Quantity:	1000

**General Information**

Series:	CAS SMD SFTY 250
Style:	SMD Chip
Description:	Industrial Grade, Safety MLCC
RoHS:	Yes
Termination:	Tin
Safety Class:	X1/Y2
AEC-Q200:	No
Halogen Free:	Yes

**Specifications**

Capacitance:	56 pF
Measurement Condition:	1 MHz 1Vrms
Capacitance Tolerance:	2%
Voltage AC:	250 VAC (X1), 250 VAC (Y2)
Temperature Range:	-55/+125°C
Temperature Coefficient:	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):	30 ppm/C, 1kHz 1.0Vrms
Insulation Resistance:	100 GOhms
Quality Factor:	1000