# **Data Sheet**



# Coaxial Cable Connector 16\_BNC-50-3-26/133\_N

# **Description**

Right angle cable plug

Interface standards IEC 61169-8\_MIL-STD-348A/301\_CECC 22120



### **Technical Data**

#### **Electrical Data**

Frequency range DC to 2.5 GHz 2.5 to 4 GHz
Return loss 32 dB 19 dB

#### **Mechanical Data**

Centre contact soldered
Outer contact crimped
Weight 0.0161 kg

#### **Environmental Data**

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

#### **Material Data**

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

# **Related Documents**

Outline drawing DOU-00109810
Assembly instruction DOC-0000179021

# **Ordering Information**

Single package 16\_BNC-50-3-26/133\_NE

# **Additional Information**

Suitable cables RG\_223\_/U, ENVIROFLEX\_142, G\_03232\_D-01, RG\_400\_/U, RADOX\_RF\_400

## Remarks

El. optimized for cable RG\_223\_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.