Data Sheet



Coaxial Cable Connector 24_BNC-50-3-25/133_N

Description

Straight bulkhead cable feed through

Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 4 \ \text{GHz} \end{array}$

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0163 kg

Environmental Data

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00009162
Catalogue drawing DCA-00008942
Assembly instruction DOC-0000179061
Mounting hole DOU-00008751

Ordering Information

 Single package
 24_BNC-50-3-25/133_NE

 Bulk 100 pcs package
 24_BNC-50-3-25/133_NH

Additional Information

Suitable cables RG 400 /U, ENVIROFLEX 142, RADOX RF 400, ASNE0293 XF

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.