Data Sheet



Coaxial Cable Connector 11_N-50-2-11/133_N

Description

Straight cable plug

Interface standards
IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

 $\begin{array}{ll} \mbox{Impedance} & \mbox{50} \ \Omega \\ \mbox{Interface frequency max.} & \mbox{11 GHz} \end{array}$

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0265 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00007281
Catalogue drawing DOU-00007283
Assembly instruction DOC-0000179123

Ordering Information

Bulk 100 pcs package 11_N-50-2-11/133_NH

Additional Information

Suitable cables RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.