Data Sheet



Coaxial Cable Connector 11_QLA-01-2-8/122_N

Description

Straight cable plug

Interface standards
NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 1.4 \ \text{GHz} \end{array}$

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0031 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -55 °C to 150 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00006541
Catalogue drawing DOU-00006116
Assembly instruction DOC-0000201093

Ordering Information

 Single package
 11_QLA-01-2-8/122_NE

 Bulk 100 pcs package
 11_QLA-01-2-8/122_NH

Additional Information

Suitable cables RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.