NX-series EtherCAT Coupler Unit

Combine flexibility in Remote I/O configuration with the speed and determinism of EtherCAT.


• The EtherCAT Coupler Unit is the link between the EtherCAT Machine Control network and the NX-series I/O Units. With I/O Units ranging from basic I/O's to high-speed synchronous models, the NX-series is the perfect match for the Sysmac Machine Automation Controllers.



Features

- Up to 63 NX-IO Units can be connected to one EtherCAT Coupler Unit. Standard and high-performance units can be mixed.*1
- High-speed remote I/O control is possible at the fastest communication cycle of 125 us.¹²
- · Each Coupler plus its I/O form just a single EtherCAT node on the network.
- I/O control and safety control can be integrated by connecting Units for safety.
- The Coupler supports the EtherCAT Distributed Clock (DC) and propagates this to synchronous I/O units.
- The node address can be fixed by rotary switches, or set by software. Choose the method that best suits your way of engineering.
- Slave configuration by Sysmac Studio can be done centrally via the controller, or on-the-spot using the Coupler's built-in USB port.
- *1 Input per Coupler Unit: Maximum 1024 bytes, Output per Coupler Unit: Maximum 1024 bytes
- *2 NX7-

System Configuration



* Refer to Versions information on the unit versions of CPU Units when you connect an EtherCAT Slave Terminal to the built-in EtherCAT port on an OMRON NJ/NX-series CPU Unit. An EtherCAT Slave Terminal cannot be connected to any of the OMRON CJ1W-NC 81/82 Position Control Units even though they can operate as EtherCAT masters.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT[®] is a registered trademark of Beckhoff Automation GmbH for their patented technology. EtherNet/IPTM is the trademarks of ODVA.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

Ordering Information

International Standards

- The standards are abbreviated as follows: U: UL, U1: UL(Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, CE: EC Directives, and KC: KC Registration.
- · Contact your OMRON representative for further details and applicable conditions for these standards.

Unit type	Product Name	Communications cycle in DC Mode *1 *2	Current consumption	Maximum I/O power supply current	Model	Standards
NX Series EtherCAT Coupler Unit	EtherCAT Coupler Unit	250 to 4,000 μs	1.45 W or lower	4 A	NX-ECC201	UC1, N, L,
				10 A	NX-ECC202	CE, KC
		125 to 10,000 μs	1.25 W or lower		NX-ECC203	UC1, CE, KC

*1. This depends on the specifications of the EtherCAT master. For example, the values are as follows when the EtherCAT Coupler Unit is connected to the built-in EtherCAT port on an NJ5-series CPU Unit: 500 µs, 1,000 µs, 2,000 µs, and 4,000 µs. Refer to the *NJ/NX-series CPU* Unit Built-in EtherCAT Port User's Manual (Cat. No. W505) for the specifications of the built-in EtherCAT ports on NJ/NX-series CPU Units.

*2. This depends on the Unit configuration.

Recommended EtherCAT Communications Cables

Use Straight STP (shielded twisted-pair) cable of category 5 or higher with double shielding (braiding and aluminum foil tape) for EtherCAT.

Cable with Connectors

Item	Appearance	Recommended manufacturer	Cable length(m) *1	Model
			0.3	XS6W-6LSZH8SS30CM-Y
Standard type			0.5	XS6W-6LSZH8SS50CM-Y
Cable with Connectors on Both Ends (RJ45/RJ45) Wire Gauge and Number of Pairs: AWG27, 4-pair Cable	\bigcirc	OMBON	1	XS6W-6LSZH8SS100CM-Y
Cable Sheath material: LSZH *2		OMRON	2	XS6W-6LSZH8SS200CM-Y
Cable color: Yellow *3			3	XS6W-6LSZH8SS300CM-Y
			5	XS6W-6LSZH8SS500CM-Y
			0.3	XS5W-T421-AMD-K
			0.5	XS5W-T421-BMD-K
Rugged type Cable with Connectors on Both Ends (RJ45/RJ45)	23	OMBON	1	XS5W-T421-CMD-K
Wire Gauge and Number of Pairs: AWG22, 2-pair Cable	*()	OMRON 2	2	XS5W-T421-DMD-K
			5	XS5W-T421-GMD-K
			10	XS5W-T421-JMD-K
		0.3 0.5 0.5 1 2 5	0.3	XS5W-T421-AMC-K
Rugged type	all.		0.5	XS5W-T421-BMC-K
Cable with Connectors on Both Ends (M12 Straight/	24		1	XS5W-T421-CMC-K
RJ45)			2	XS5W-T421-DMC-K
Wire Gauge and Number of Pairs: AWG22, 2-pair Cable			5	XS5W-T421-GMC-K
			10	XS5W-T421-JMC-K
			0.3	XS5W-T422-AMC-K
Rugged type			0.5	XS5W-T422-BMC-K
Cable with Connectors on Both Ends (M12 Right-angle/		OMBON	1	XS5W-T422-CMC-K
RJ45)	F ()	OWINON	2	XS5W-T422-DMC-K
Wire Gauge and Number of Pairs: AWG22, 2-pair Cable	· V		5	XS5W-T422-GMC-K
			10	XS5W-T422-JMC-K

Standard type cables length 0.2, 0.3, 0.5, 1, 1.5, 2, 3, 5, 7.5, 10, 15 and 20m are available. Rugged type cables length 0.3, 0.5, 1, 2, 3, 5, 10 and 15m are available. *1

The lineup features Low Smoke Zero Halogen cables for in-cabinet use and PUR cables for out-of-cabinet use. *2

*3 Cables colors are available in blue, yellow, or Green

Note: For details, refer to Cat.No.G019.

Cables / Connectors

Wire Gauge and Number of Pairs: AWG24, 4-pair Cable

Item	Appearance	Recommended manufacturer	Model
	-	Hitachi Metals, Ltd.	NETSTAR-C5E SAB 0.5 × 4P*
Cables	-	Kuramo Electric Co.	KETH-SB*
	-	SWCC Showa Cable Systems Co.	FAE-5004*
RJ45 Connectors	-	Panduit Corporation	MPS588-C*

* We recommend you to use above cable and connector together.

Wire Gauge and Number of Pairs: AWG22, 2-pair Cable

Item	Appearance	Recommended manufacturer	Model	
Cables	-	Kuramo Electric Co.	KETH-PSB-OMR*	
Cables	-	Nihon Electric Wire&Cable Co.,Ltd.	PNET/B*	
RJ45 Assembly Connector		OMRON	XS6G-T421-1*	

* We recommend you to use above cable and connector together. Note: Connect both ends of cable shielded wires to the connector hoods.

Optional Products

Product name	Specification			Model	Standards
Unit/Terminal Block Coding Pins	Pins for 10 Units (30 terminal block pins and 30 Unit pins)			NX-AUX02	
	Specification				
Product Name	No. of terminals	Ground terminal mark	Terminal current capacity	Model	Standards
Terminal Block	8	Present	10 A	NX-TBC082	

Accessories

End Cover (NX-END01)

An End Cover is connected to the end of the EtherCAT Slave Terminal. One End Cover is provided together with the EtherCAT Coupler Unit.

General Specification

	Item	Specification
Enclosure		Mounted in a panel
Grounding method		Ground to 100 Ω or less
_	Ambient operating temperature	0 to 55°C
	Ambient operating humidity	10% to 95% (with no condensation or icing)
	Atmosphere	Must be free from corrosive gases.
	Ambient storage temperature	-25 to 70°C (with no condensation or icing)
	Altitude	2,000 m max.
Operating	Pollution degree	Pollution degree 2 or less: Conforms to JIS B3502 and IEC 61131-2.
environment	Noise immunity	Conforms to IEC61000-4-4. 2 kV (power supply line)
	Overvoltage category	Category II: Conforms to JIS B3502 and IEC 61131-2.
	EMC immunity level	Zone B
	Vibration resistance	Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz, acceleration of 9.8 m/s ² , 100 min each in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total)
	Shock resistance	Conforms to IEC 60068-2-27. 147 m/s ² , 3 times each in X, Y, and Z directions
Applicable standards *		cULus: Listed UL508 and ANSI/ISA 12.12.01 EC: EN 61131-2 and C-Tick, KC Registration, NK, LR

* Refer to the OMRON website (http://www.ia.omron.com/) or consult your OMRON representative for the most recent applicable standards for each model.

Specifications

EtherCAT Coupler Unit NX-ECC201/NX-ECC202/NX-ECC203

Itom		Specification			
	Item	NX-ECC201	NX-ECC202	NX-ECC203	
Number of connectable NX Units		63 Units max.*1			
Send/receive PDO data sizes		Input: 1,024 bytes max. (including Output: 1,024 bytes max. (including	input data, status, and unused are ng output data and unused areas)	as)	
Mailbox data si	ize	Input: 256 bytes Output: 256 bytes			
Mailbox		Emergency messages and SDO r	equests		
Refreshing methods ^{*2}		 Free-Run refreshing Synchronous I/O refreshing Time stamp refreshing 		 Free-Run refreshing Synchronous I/O refreshing Time stamp refreshing Task period prioritized refreshing 	
Nodo addross	softing range	When Connected to the Built-in EtherCAT Port on an NX-series CPU Unit • Set on switches: 1 to 199 • Set with the Sysmac Studio: 1 to 512			
Node address setting range		When Connected to the Built-in EtherCAT Port on an NJ-series CPU Unit • Set on switches: 1 to 192 • Set with the Sysmac Studio: 1 to 192			
I/O jitter perfor	mance	Inputs: 1 μs max. Outputs: 1 μs max.			
Communicatio	ns cycle in DC Mode	250 to 4,000 μs ^{*3 *4} 125 to 10,000 μs ^{*3 *4}			
	Power supply voltage	24 VDC (20.4 to 28.8 VDC)			
	NX Unit power supply capacity	10 W max. Refer to <i>Installation orientation and restrictions</i> for details.			
Unit power supply	NX Unit power supply efficiency	70%			
	Isolation method	No isolation between NX Unit pow	ver supply and Unit power supply te	rminals	
	Current capacity of power supply terminals	4 A max.			
	Power supply voltage	5 to 24 VDC (4.5 to 28.8 VDC) *5			
/O power	Maximum I/O power supply current	4 A	10 A		
supply	Current capacity of power supply terminals	4 A max. 10 A max.			
NX Unit power	consumption	1.45 W max.		1.25 W max.	
Current consu	mption from I/O power supply	10 mA max. (for 24 VDC)			
Dielectric stren	ngth	510 VAC for 1 min, leakage current: 5 mA max. (between isolated circuits)			
Insulation resistance		100 VDC, 20 MΩ min. (between isolated circuits)			

*1. Refer to the NX-series Safety Control Units User's Manual (Cat. No. Z930) for the number of Safety Control Units that can be connected.


*2. This function was added or improved for a version upgrade. Refer to *NX-series EtherCAT Coupler Unit User's Manual* (Cat. No. W519) for information on version upgrades

*3. This depends on the specifications of the EtherCAT master. The values are as follows when you are connected to the built-in EtherCAT port on an NJ5-series CPU Unit: 500 μs, 1,000 μs, 2,000 μs, and 4,000 μs. Refer to the NJ/NX-series CPU Unit Built-in EtherCAT Port User's Manual (Cat. No. W505) for the specifications of the built-in EtherCAT ports on NJ/NX-series CPU Units.


*4. This depends on the Unit configuration.

*5. Use an output voltage that is appropriate for the I/O circuits of the NX Units and the connected external devices.

NX-ECC



NX-ECC



EtherCAT Communications Specifications

Item	Specification
Communications standard	IEC 61158 Type 12
Physical layer	100BASE-TX (IEEE 802.3)
Modulation	Baseband
Baud rate	100 Mbps
Topology	Depends on the specifications of the EtherCAT master.
Transmission media	Category 5 or higher twisted-pair cable (Recommended cable: double-shielded cable with aluminum tape and braiding)
Transmission distance	Distance between nodes: 100 m or less

Version Information

	Unit version	Corresponding unit version/version *1				
Model number of EtherCAT Coupler Unit		Using an NX-series CPU Unit		Using an NJ-series CPU Unit		
		Unit version of CPU Unit	Sysmac Studio version	Unit version of CPU Unit	Sysmac Studio version	
	1.2	Ver. 1.10 or later	Ver. 1.13 or later	Ver. 1.07 or later	Ver. 1.08 or higher	
NX-ECC201	1.1			Ver. 1.06 or later	Ver. 1.07 or higher	
	1.0			Ver. 1.05 or later	Ver. 1.06 or higher	
NX-ECC202	1.2 ^{*2}			Ver. 1.07 or later	Ver. 1.08 or higher	
NX-ECC203	1.3 ^{*3}			Ver. 1.07 or later	Ver. 1.13 or higher	


*1 Some Units do not have all of the versions given in the above table. If a Unit does not have the specified version, support is provided by the oldest available version after the specified version. Refer to the user's manuals for the specific Units for the relation between models and versions.

*2 For the NX-ECC202, there is no unit version of 1.1 or earlier.

*3 For the NX-ECC203, there is no unit version of 1.2 or earlier.


External Interface

EtherCAT Coupler Unit NX-ECC20



Symbol	Name	Function
(A)	NX bus connector	This connector is used to connect each Unit.
(B)	Indicators	The indicators show the current operating status of the Unit.
(C)	Communications connectors	These connectors are connected to the communications cables of the EtherCAT network. There are two connectors, one for the input port and one for the output port.
(D)	Peripheral USB port	This port is used to connect to the Sysmac Studio Support Software.
(E)	Terminal block	The terminal block is used to connect external devices. The number of terminals depends on the type of Unit.
(F)	Rotary switches	These rotary switches are used to set the 1s digit and 10s digit of the node address of the EtherCAT Coupler Unit as an EtherCAT slave. The address is set in decimal.
(G)	DIP switch	The DIP switch is used to set the 100s digit of the node address of the EtherCAT Coupler Unit as an EtherCAT slave.

Terminal Block



Symbol	Name	Function
(A)	Terminal number indications	The terminal numbers (A1 to A8 and B1 to B8) are displayed. The terminal number indicators are the same regardless of the number of terminals on the terminal block, as shown above.
(B)	Release holes	Insert a flat-blade screwdriver into these holes to connect and remove the wires.
(C)	Terminal holes	The wires are inserted into these holes.
(D)	Ground terminal mark	This mark indicates the ground terminals. Only the NX-TBC082 has this mark.

Applicable Terminal Blocks for Each Unit Model

Unit model	Current capacity of Unit's power supply terminals		Terminal Blocks				
onit moder	Unit power supply	I/O power supply	Model	No. of terminals	Ground terminal mark	Terminal current capacity	
NX-ECC201	4 A		NX-TBC082	8	Present	10 A	
NX-ECC202 or 4 A 10 A		NX-TBC082	8	Present	10 A		

Applicable Wires

Using Ferrules

If you use ferrules, attach the twisted wires to them.

Observe the application instructions for your ferrules for the wire stripping length when attaching ferrules.


Always use plated one-pin ferrules. Do not use unplated ferrules or two-pin ferrules.

The applicable ferrules, wires, and crimping tool are given in the following table.

Terminal types	Manufacturer	Ferrule model	Applicable wire (mm ² (AWG))	Crimping tool		
Terminals other than ground terminals	Phoenix Contact	Al0,34-8	0.34 (#22)	Phoenix Contact (The figure in parentheses is the applicable wire		
		AI0,5-8	0.5 (#20)	size.)		
lemmais		AI0,5-10		CRIMPFOX 6 (0.25 to 6 mm ² , AWG 24 to 10)		
		AI0,75-8	0.75 (#18)			
		Al0,75-10				
		AI1,0-8	1.0 (#18)			
		Al1,0-10				
		Al1,5-8	1.5 (#16)			
		Al1,5-10				
Ground terminals		Al2,5-10	2.0 *1			
Terminals other	Weidmuller	H0.14/12	0.14 (#26)	Weidmueller (The figure in parentheses is the applicable wire size.)		
than ground		H0.25/12	0.25 (#24)	PZ6 Roto (0.14 to 6 mm ² , AWG 26 to 10)		
terminals		H0.34/12	0.34 (#22)			
		H0.5/14	0.5 (#20)	-		
		H0.5/16				
		H0.75/14	0.75 (#18)			
		H0.75/16				
		H1.0/14	1.0 (#18)			
		H1.0/16				
		H1.5/14	1.5 (#16)			
		H1.5/16				

*1. Some AWG 14 wires exceed 2.0 mm² and cannot be used in the screwless clamping terminal block.

When you use any ferrules other than those in the above table, crimp them to the twisted wires so that the following processed dimensions are achieved.



Using Twisted Wires/Solid Wires

If you use the twisted wires or the solid wires, use the following table to determine the correct wire specifications.

Terminals		Wire type		Wire plating			Conductor longth
Classification	Current capacity	Twisted wires	Solid wire	Plated	Unplated	Wire size	Conductor length (stripping length)
All terminals except ground terminals	2 A max.	- Possible	Possible		Possible	0.08 to 1.5 mm ² AWG28 to 16	8 to 10 mm
	Greater than 2 A and 4 A or less			- Possible	Not		
	Greater than 4 A		Not Possible		Possible		
Ground terminals *			Possible		Possible	2.0 mm ²	9 to 10 mm

* With the NX-TB 1 Terminal Block, use twisted wires to connect the ground terminal. Do not use a solid wire.


<>	

Conductor length (stripping length)

<Additional Information> If more than 2 A will flow on the wires, use plated wires or use ferrules.


Dimensions

EtherCAT Coupler Unit • EtherCAT Coupler Unit Only




* The dimension is 1.35 mm for Units with lot numbers through December 2014.

With Cables Connected



- *1. This dimension depends on the specifications of the commercially available USB cable. Check the specifications of the USB cable that is used.
- *2. This is the dimension from the back of the Unit to the communications cables.
 - 100 mm: When an MPS588-C Connector is used.
 - 120 mm: When an XS6G-T421-1 Connector is used.

End Cover



* This is the shape for Units with lot numbers through December 2014.

Related Manuals

Man. No	Model	Manual	Application	Description
W519	NX-ECC20	NX-series EtherCAT Coupler Unit User's Manual	Leaning how to use an NX-series EtherCAT Coupler Unit and Ether-CAT Slave Terminals	The following items are described: the overall system and configuration methods of an EtherCAT Slave Terminal (which consists of an NX-series EtherCAT Coupler Unit and NX Units), and information on hardware, setup, and functions to set up, control, and monitor NX Units through EtherCAT.

Terms and Conditions of Sale

- 1. Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms, All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts, Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
- 2
- 3.
- and (ii) Buyer has no past due amounts. Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
- Orders. Omron will accept no order less than \$200 net billing. Governmental Approvals. Buyer shall be responsible for, and shall bear all 6 costs involved in, obtaining any government approvals required for the impor-tation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or 7. indirectly by Omron for the manufacture, production, sale, delivery, importa-tion, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron. <u>Financial.</u> If the financial position of Buyer at any time becomes unsatisfactory
- 8. <u>Einancial</u> If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liabil-ity and in addition to other remedies) cancel any unshipped portion of Prod-ucts sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts unpaid accounts.
- <u>Cancellation</u>, <u>Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
 <u>Force Majeure</u>. Omron shall not be liable for any delay or failure in delivery
- Force majeure. Other shall not be liable for any delay or lating in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
 Shipping: Delivery. Unless otherwise expressly agreed in writing by Omron: a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship expert in "break down" situations.
- except in "break down" situations. b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
 - constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth-
- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 d. Delivery and shipping dates are estimates only; and
 e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
 12. Claims. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier received the Products
- portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- <u>Warranties</u>. (a) <u>Exclusive Warranty</u>. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed 13 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity 1. with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application to use of the Froduct. At Buyer's application of use of the product applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Prod-uct in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyers application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given: (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document. (ii) Use in consumer products or any use in significant quantities. (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equip-ment and installicitors cubications of the consumer to construct the construction.

inent, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or oth-erwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Omron's sole obli-gation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsi-ble for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were prop-erly handled, stored, installed and maintained and not subject to contamina-tion, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Compa-nies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.

- Iished information.
 Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted. 14
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, inves-tigation, litigation or proceeding (whether or not Omron is a party) which arises 15 or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or set-tle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party. <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclu-sive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly provent disclosure to any third party. 16
- 17
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information. <u>Miscellaneous</u>. (a) <u>Waiver</u>. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) <u>Assignment</u>. Buyer may not assign its rights hereunder without Omron's written consent. (c) <u>Law</u>. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) <u>Amendment</u>. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing singed by the parties. (e) Severability. If any provi-18 or waived unless in writing signed by the parties. (e) <u>Severability</u>. If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff, Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Compa-</u> nies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. <u>Performance Data</u>. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitabil-ity and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application require-2 3 ments. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be 4 Change in specifications. Product specifications and accessions may be changed at any time based on improvements and other reasons. It is our prac-tice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifica-tions of the Product may be changed without any notice. When in doubt, spe-cial part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual creating of purphased Product to confirm actual specifications of purchased Product. Errors and Omissions. Information presented by Omron Companies has been
- 5 checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



OMRON AUTOMATION AND SAFETY • THE AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO · SALES OFFICE Apodaca, N.L. · 52.81.11.56.99.20 · 01-800-226-6766 · mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br OMRON ARGENTINA • SALES OFFICE Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES 54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

Automation Control Systems

- Machine Automation Controllers (MAC)
 Programmable Controllers (PLC)
- Operator interfaces (HMI)
 Distributed I/O
 Software

Drives & Motion Controls

Servo & AC Drives
 Motion Controllers & Encoders

Temperature & Process Controllers

Single and Multi-loop Controllers

Sensors & Vision

- Proximity Sensors
 Photoelectric Sensors
 Fiber-Optic Sensors
- Amplified Photomicrosensors
 Measurement Sensors
- Ultrasonic Sensors
 Vision Sensors

Industrial Components

- RFID/Code Readers
 Relays
 Pushbuttons & Indicators
- Limit and Basic Switches
 Timers
 Counters
 Metering Devices
- Power Supplies

Safety

• Laser Scanners • Safety Mats • Edges and Bumpers • Programmable Safety Controllers • Light Curtains • Safety Relays • Safety Interlock Switches

NX-ECC_DS_E_6_1 04/15 Note: Specifications are subject to change. © 2015 Omron

© 2015 Omron Electronics LLC