Data Sheet

HUBER+SUHNER

Coaxial Cable Connector 24_SMA-50-2-14/111_N

Description

Straight bulkhead cable feed through

Interface standards IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data	
Impedance	50 Ω
Interface frequency max.	18 GHz
Mechanical Data	
Centre contact	soldered
Outer contact	crimped
Weight	0.0045 kg
Environmental Data	
Operating temperature	-65 °C to 165
2011/65/EU (RoHS - including	compliant
2015/863 and 2017/2102)	

65 °C

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00009440
Catalogue drawing	DCA-00008868
Assembly instruction	DOC-0000179078
Mounting hole	DOU-00008748

Ordering Information

Single package Bulk 100 pcs package 24 SMA-50-2-14/111 NE 24_SMA-50-2-14/111_NH

Additional Information

Suitable cables

RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.