# **Data Sheet**

# **HUBER+SUHNER**

# Coaxial Cable Connector 25\_TNC-50-2-1/133\_N

### Description

Straight panel cable jack, flange mount

Interface standards IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



# **Technical Data**

Electrical Data Impedance Interface frequency max.	50 Ω 11 GHz
<b>Mechanical Data</b> Centre contact Outer contact Weight	soldered clamped 0.0193 kg
Environmental Data Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 165 °C compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

## **Related Documents**

Outline drawing	DOU-00048074
Catalogue drawing	DCA-00009017
Assembly instruction	DOC-0000179064

### **Ordering Information**

Single package

25\_TNC-50-2-1/133\_NE

### **Additional Information**

Suitable cables

RG\_316\_/U, RG\_188\_A/U, RG\_174\_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.