



## Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 10

BERGQUIST GAP PAD TGP 5000 known as Gap Pad 5000S35

SDS No. : 554192  
V002.0

Revision: 27.05.2020  
printing date: 04.06.2020

Replaces version from: 17.06.2019

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

BERGQUIST GAP PAD TGP 5000 known as Gap Pad 5000S35

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Thermal Interface Material

#### 1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

Fax-no.: +49 211 798 2009

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.2. Label elements

##### Label elements (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Manufactured item - article

##### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Aluminium nitride 24304-00-5	246-140-8	10- < 20 %	Aquatic Chronic 2 H411

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

##### Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

##### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

##### Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause eye irritation.

Prolonged or repeated contact may cause skin irritation.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

##### Suitable extinguishing media:

water, carbon dioxide, foam, powder

##### Extinguishing media which must not be used for safety reasons:

High pressure waterjet

#### 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

In case of fire, keep containers cool with water spray.

#### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

##### Additional information:

In case of fire, keep containers cool with water spray.

### SECTION 6: Accidental release measures

**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.  
Wear protective equipment.  
Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.  
Sweep up spilled material. Avoid creating dust.  
Keep in suitable and closed containers for disposal.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Avoid skin and eye contact.  
See advice in section 8

## Hygiene measures:

Good industrial hygiene practices should be observed.  
Wash hands before work breaks and after finishing work.  
Do not eat, drink or smoke while working.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.  
Keep container tightly sealed.  
Refer to Technical Data Sheet

**7.3. Specific end use(s)**

Thermal Interface Material

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL

#### Biological Exposure Indices:

None

### 8.2. Exposure controls:

Engineering controls:  
Ensure good ventilation/extraction.

Respiratory protection:  
Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A (EN 14387)

Hand protection:  
Chemical-resistant protective gloves (EN 374).  
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):  
nitrile rubber (NBR; >= 0.4 mm thickness)  
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):  
nitrile rubber (NBR; >= 0.4 mm thickness)  
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:  
Wear protective glasses.  
Protective eye equipment should conform to EN166.

Skin protection:  
Wear suitable protective clothing.  
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	solid solid
Odor	light green slightly
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	Product is a solid.
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

### 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

None.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

carbon oxides.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Acute oral toxicity:**

This material is considered to have low toxicity if swallowed.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Aluminium nitride 24304-00-5	LD50	> 2.000 mg/kg	rat	not specified

**Acute dermal toxicity:**

This product is considered to have low dermal toxicity.

No substance data available.

**Acute inhalative toxicity:**

Not considered harmful under normal conditions of industrial use.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Aluminium nitride 24304-00-5	LC50	> 0,317 mg/l	dust/mist	4 h	rat	equivalent or similar to OECD Guideline 403 (Acute Inhalation Toxicity)

**Skin corrosion/irritation:**

Prolonged or repeated contact may cause skin irritation.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Aluminium nitride 24304-00-5	not irritating		Human, EpiSkin™ (SM), Reconstructed Human Epidermis (RHE)	OECD Guideline 439 (In Vitro Skin Irritation: Reconstructed Human Epidermis (RHE) Test Method)
Aluminium nitride 24304-00-5	not corrosive		Human, in vitro skin model	OECD Guideline 431 (In Vitro Skin Corrosion: Reconstructed Human Epidermis (RHE) Test Method)

**Serious eye damage/irritation:**

Prolonged or repeated contact may cause eye irritation.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Aluminium nitride 24304-00-5	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Aluminium nitride 24304-00-5	NOAEL 0,07 mg/l	inhalation	4 w 6 h/d, 5 d/w	rat	OECD Guideline 412 (Repeated Dose Inhalation Toxicity: 28/14-Day)

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information****12.1. Toxicity****Toxicity (Fish):**

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aluminium nitride 24304-00-5	LC50	> 1,8 - 8,2 mg/l	96 h	Pimephales promelas	other guideline:
Aluminium nitride 24304-00-5	NOEC	0,053 mg/l	73 d	Oncorhynchus mykiss	other guideline:

**Toxicity (Daphnia):**

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aluminium nitride 24304-00-5		9,95 mg/l	96 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aluminium nitride 24304-00-5	EC50	7,1 mg/l	48 h	not specified	OECD Guideline 201 (Alga, Growth Inhibition Test)

**Toxicity to microorganisms**

No data available.

**12.2. Persistence and degradability**

No data available.

**12.3. Bioaccumulative potential**

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
Aluminium nitride 24304-00-5	> 65,2 - 84,8	30 d		other	other guideline:

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of in accordance with local and national regulations.



**SECTION 14: Transport information**

- 14.1. UN number**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**  
not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H411 Toxic to aquatic life with long lasting effects.

**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your\_company.com).

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**