

Type: **M22-LEDC-R**
 Article No.: **216561**



Ordering information			
Connection technique			Screw terminals
Description			Base fixing
Rated operational voltage	U_e	V	12 – 30 V AC/DC
Rated operational current	I_e	mA	8 – 15
Power consumption	$P_{max.}$	W	0.26 W at 24 V
Lifespan to EN 60064 at $t_a = +25\text{ °C}$	t_{mean} (AC)	h	100000
Colour			Red

Colour



Notes concerning the product group

For pushbutton actuators, indicator lights, illuminated pushbuttons and illuminated selector switch actuators, the following applies:

M22...-R only in combination with M22-LED...-R

M22...-G only in combination with M22-LED...-G

M22...-W only in combination with M22-LED...-W

M22...-Y only in combination with M22-LED...-W

M22...-B in combination with M22-LED...-W

M22...-B or in combination with M22-LED...-B

General			
Standards			IEC/EN 60947 VDE 0660
Degree of protection, IEC/EN 60529			IP 20
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Ambient temperature			
Open		°C	-25/70
Mounting position			As required
Mechanical shock resistance according to IEC 60068-2-27 Shock duration 11 ms, half-sinusoidal		g	> 30
Terminal capacities			
Solid		mm ²	0.75 – 2.5
Stranded		mm ²	0.5 – 2.5
Contacts			
Rated impulse withstand voltage	U_{imp}	V AC	6000
Rated insulation voltage	U_i	V	500
Overtoltage category/pollution degree			III3
Notes			
			> 200 V AC/60 Hz: -25/+55 °C

Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
Copyright 2006 by Moeller GmbH. Subject to modifications. HPL-C2006GB-INT V2.3