



BCT advanced label printing scales offer a removable, easy-to-clean stainless steel platform, providing an excellent value for industrial counting tasks. Store and recall up to 1006 PLUs or piece weights to improve efficiency in production or warehouse applications. The BCT features a built-in printer that prints weight, QR codes, bar codes and labels, which can be customized on a computer using the included software. Choose from two platform sizes to meet the demands of inventory tasks, batching, shipping and receiving. RS-232 interface provide speedy connection to computers and printers.

## Built-in printer facilitates heavy-duty industrial counting tasks



### Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to "always on," "always off" or "light only when weighing"
- Adjustable levelling feet help optimise setup
- Colour-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows easy cleaning
- RS-232 interface is available to provide speedy connection to computers and printers
- Rugged construction stands up to industrial use
- Sealed keypad protects against dirt and spills
- Built in printer can print weight, QR codes, bar codes and labels in numerous languages
- Parts counting with freely selectable sample sizes
- Parts counting optimisation automatically refines piece weight as parts are added
- Zero-tracking feature ensures display returns to zero reading
- Selectable digital filtering helps minimise effects of vibration and disturbances
- Easy label creation/editing is possible on a computer using the included software
- Rechargeable battery included for operation almost anywhere
- Programmable auto power-off to save energy

### Applications

- Weighing
- Parts counting
- Check counting
- Averaging
- Barcode / label printing

### About ADAM:

For more than 45 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	BCT 16	BCT 32	BCT 60	BCT 75	BCT 150	BCT 300
Capacity	16kg	32kg	60kg	75kg	150kg	300kg
Readability	0.5g	1g	2g	5g	0.01kg	0.02kg
Repeatability (S.D.)	0.5g	1g	2g	5g	0.01kg	0.02kg
Linearity (+/-)	1g	2g	4g	10g	0.02kg	0.04kg
Pan Size	300x400mm			400x500mm		
Weighing Units	g, kg, lb, oz					
Stabilisation Time (sec)	2					
PLU memories	1006					
Interface	RS-232					
Calibration	External calibration					
Display	Backlit LCD with main display of 22mm high digits, and secondary display of 16mm high digits					
Power Supply	12VDC 50/60Hz 3A adapter					
Operating Temperature	-10° to 40°C					
Housing	ABS plastic indicator with die-cast aluminum base					
Overall Dim.	300x520x680mm (wxdxh)			400x620x860mm (wxdxh)		
Net Weight	8.5kg			13.5kg		

## Accessories

Item number	Description
3074010266	.....RS-232 cable (null-modem)
600002028	.....AdamDU Data Collection Program
700660290	.....Calibration certificate
700660288	.....Calibration certificate (IHS, LHS, AFK 600, GFK 600, PTM)
700200107	.....Casters / wheels (set of 4)

## Key Accessories



### AdamDU Data Collection Program

Adam DU software connects a balance to the laboratory network, helping to achieve seamless data collection, transfer and analysis. DU features an easy-to-use interface with a main command window, allowing users to quickly collect information from up to eight Adam balances simultaneously using RS-232 or USB connections.



### Casters / wheels (set of 4)

Optional castor wheels provide easy mobility for bench and floor scales. A brake lock prevents movement during use.

Supplied by