




light source	LED
work equipment	Energy efficiency category A/A+/A++
connected load	electronic ballast
Power consumption	220-240 V; 50/60 Hz
luminous flux	approx. 35 W
luminous efficacy	approx. 3000 lm
colour temperature	approx. 85 lm/W
color rendering index (CRI)	neutral white, approx. 5000 K
glare control	>= 80
System of protection	structured screen
class of protection	IP20
technology	I
operation	switchable
luminaire body	rocker switch
lamp cover	aluminium/plastic, anodised, aluminium coloured anodised
weight (net)	structured screen
mains lead	approx. 3.2 kg
	approx. 3,0 m; mains plug
	CEE 7/XVII
design	mounted version
Fastening	screw down lash
dimension	A=899 mm
special features	through-wired



CEE 7/XVII



illuminance

luminous intensity

