


Type	Size	Description	Part No.
Incandescent	T10 (T-3¼)	Miniature Screw lamp (MES ~ 30 MOL)	(see table)



Drawing not to scale
All dimensions in mm

PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
653706	40	6.3V 0.94W	6.3	135	150	165	4.9	6.5	8.1	C-2R	3000
653718	46	6.3V 1.57W	6.3	225	250	275	8.5	11.3	14.1	C-2R	3000
653780	1823	48V 4.8W	48	90	100	110	30	40	50	CC-2F	1000

NOTES:

- 1) E10/13 nickel-plated screw cap in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-22-x.
- 2) Metal base to be durably marked with rating and trademark.