

BS 5308 Part 1 Type 1 LSZH

Screened Paired and Quad Instrumentation Cable

multicomp PRO

**RoHS
Compliant**



Application:

BS 5308 cables are designed to carry communication and control signals in a variety of installation types including those found in the petrochemical industry. The signals can be of analogue, data or voice type and from a variety of transducers such as pressure, proximity or microphone. BS 5308 cables are designed to form part of an intrinsically safe system. Part 1 Type 1 cables are generally designed for indoor use and in environments where mechanical protection is not required.

Cable Standards:

Made in accordance with the following:

BS/PAS 5308, BS EN 60228, BS 6234, BS EN 50363,
BS EN/IEC 60332-1, BS EN/IEC 60332-3-24

Construction:

Conductor	: Class 1 solid, Class 2 stranded or Class 5 flexible copper conductor according to BS EN 60228 (previously to BS 6360)
Pairing	: Two insulated conductors uniformly twisted together
Quad	: Four insulated conductors uniformly twisted together
Insulation	: XLPE (Cross-Linked Polyethylene) Type 03 according to BS 6234
Shielding (Collective Overall Screen)	: AL/PET (Aluminium/Polyester Tape)
Drain Wire	: Tinned copper
Sheath	: LSZH (Low Smoke Zero Halogen) Type LTS3 according to BS 7655

Characteristics:

Voltage Rating (Uo/U)	: 300/500V
Temperature Rating	: -30°C to +90°C (Fixed)
Min. Bending Radius	: 12 × overall diameter (Fixed)
Sheath Colour	: Black

Electrical Characteristics:

Collectively Screened Cables

Nominal Cross Sectional Area mm ²	Mutual Capacitance pF/m	Min. Insulation Resistance at 20°C mΩ/km	Max. L/R Ratio μH/Ω
	Cables with Collective Overall Screen		
0.5	75	>5	25
0.75	75	>5	25
1.5	85	>5	40

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

BS 5308 Part 1 Type 1 LSZH

Screened Paired and Quad Instrumentation Cable



Core Colours:

Pair No.	A Wire	B Wire
1	Black	Blue
2	Black	Green
Quad	Black, Blue, Green, Brown	

Conductors:

Nominal Cross Sectional Area mm ²	Conductor Class	Max. DC Resistance of Conductor at 20°C Ω/km
0.5	5	39
0.75	5	26
1.5	2	12.1

Dimensions:

Part Number	No. of Pairs / Quad	Nominal Cross Sectional Area mm ²	Nominal Overall Diameter mm
PP000929	1P	0.5	7
PP000930	1P	0.75	7.4
PP000931	1P	1.5	8.3
PP000933	Q	0.5	7.9
PP000932	2P	0.75	8.4
PP000934	Q	0.75	8.4

P = Pairs

Q = Quad

Part Number Table

Description	No. of Pairs / Quad	Reel Length (m)	Part Number
BS 5308 Part 1 Type 1 LSZH Screened Paired / Quad Instrumentation Cable	1 Pr.	50	PP000929
	1 Pr.		PP000930
	1 Pr.		PP000931
	2 Pr.		PP000932
	Quad		PP000933
	Quad		PP000934

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

