100mm IP67 contact-sealed SMA Bulkhead Jack -SMA PLUG 1.37mm IP67 Sealed connector without antenna connected






RoHS Compliant

Electrical Performance:

Impedance : 50Ω

Frequency Range : DC \sim 3.0GHz Working Voltage : 170Vrms Max. Dielectric Withstanding Voltage : 750Vrms Max. Insulator Resistance : 1,000M Ω Min.

The material used in the construction of this cables do not contain, by mass, more than: 10% in total of aluminum, magnesium, titanium and zirconium and 7.5% in total of magnesium, titanium and zirconium.



Dimensions: Millimetres

Specification	VSWR	Insertion Loss	
DC~3.0GHz	1.4 : 1 Max	-0.8dB Max.	

Item	Description		U/M
1	Attachment : Nut-1PCs, Washer-1PCs, O-Ring-1PCs		
	IP67 sealed SMA B/H Jack (D-Cut) Crimp Type for OD 1.37mm Cable	'	EA
2	SMA ST. Plug Crimp for OD 1.37mm Cable		EA
3	Heat Shrink Tube F32 OD 2.5mm L = 15mm Colour : Black		EA
4	OD : 1.37mm Cable; Colour : Black		EA

Part Number Table

Description	Part Number	
100mm IP67 contact-sealed SMA-SMA Plug (1.37mm)	MC001027	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

