

High voltage bidirectional current sense amplifier evaluation kit based on the TSC2011



Features

- Wide common mode voltage range: -20 to $70 V_{AC}$
- Offset voltage: $\pm 200 \mu V$ max.
- 2.7 to 5.5 V supply voltage
- Quiescent current: 20 μA in Shutdown mode
- RoHS compliant

Description

The STEVAL-AETKT1V1 evaluation kit implements a bidirectional current sense amplifier consisting of a sense resistor placed either on the high side or the low side. The kit consists of a main board and a daughter board with TSC2011 high voltage, bidirectional, current sense amplifier providing a fixed gain of 60.

The TSC2011 device implements a thin film resistor for extremely precise gain and very high common-mode rejection ratio (CMRR) performance, even in high frequency ranges. The device can work with an input common mode voltage well beyond the power supply V_{CC} range (2.7 V to 5.5 V), which is ideal for automotive and similar applications requiring reverse battery support without consequent damage. It also works with 48 V battery applications, as the device can support and measure the current on line at voltages up to 70 V, no additional protective components are required in that range. Moreover, the ability to fix the output common mode voltage means that the device can be either used as unidirectional or bidirectional current sensing amplifier.

The main board in the kit can accommodate other daughter boards with TSC201x current sense amplifiers to allow testing and evaluation of different gain configurations.

Product summary	
evaluation kit for TSC2011 bidirectional current sense amplifier	STEVAL-AETKT1V1
high voltage, precision, bidirectional current sense amplifier	TSC2011
Applications	Automotive Motor Control Electro-Mobility Factory Automation Industrial Power and Tools

1 Schematic diagrams

Figure 1. STEVAL-AETKT1V1 main board (STEVAL-AET001V1B) schematic diagram

The STEVAL-AET001V1B board is not available for separate sale





Figure 2. STEVAL-AETKT1V1 daughter board (STEVAL-AET002V1B) schematic diagram

The STEVAL-AET002V1B board is not available for separate sale



Revision history

Table 1. Document revision history

Date	Version	Changes
02-Mar-2020	1	Initial release.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved