



Main

Range	TeSys
Device short name	DF14
Product or component type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NC
Connections - terminals	Faston connector

Complementary

Range compatibility	TeSys DF
[Ui] rated insulation voltage	250 VAC
[Ue] rated operational voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] conventional free air thermal current	5 A
Minimum switching current	30 mA
Minimum switching voltage	10 V
Net weight	0.029 kg

Environment

Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	18 months
----------	-----------
