

## Between Series Adaptor 33\_BNC-N-50-1/133\_N

### Description

Adaptor plug/jack  
BNC plug (male) / N jack (female)

Interface standards  
Series BNC - IEC 61169-8\_MIL-STD-348A/301\_CECC 22120  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 4 GHz ≤ 1.04 + 0.025 f (GHz)

#### Mechanical Data

Number of matings	500
Weight	0.0346 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator		

### Related Documents

Catalogue drawing	DCA-00014388
-------------------	--------------

### Ordering Information

Single package	33_BNC-N-50-1/133_NE
----------------	----------------------