## Product data sheet Characteristics

# GS1DDB4

TeSys GS - switch-disconnector-fuse - 3 P + N -BS - 32 A



lai

Main		
Range	TeSys	
Product name	TeSys GS	
Device short name	GS1 DD	
Product or component type	Switch-disconnector-fuse	
Device application	Protection	
Design	Compact	
Poles description	3P + Nc	
Protected poles description	3t	
Contacts type and composition	4 NO	
[lth] conventional free air thermal current	32 A (at 40 °C)	
[le] rated operational current	20 A at 440 V 2 poles in series per phase DC-23A 20 A at 440 V 2 poles in series per phase DC-23B 32 A at 400690 V AC-23A 32 A at 400690 V AC-23B	
Fuse type	BS	
Fuse size	A1	
Network type	DC AC	
Network frequency	50/60 Hz	
Complementary		
Type of operating handle	External frontal	

#### Complementary

- Complementary		
Type of operating handle	External frontal Direct frontal External right side External left side	
Mounting support	Rail Plate	
[Ui] rated insulation voltage	800 V AC 50/60 Hz	
[Uimp] rated impulse withstand voltage	8 kV	
Rated operational power in W	15 kW at 400 V 25 kW at 690 V	
Making capacity	320 A at 400 V AC-23B	Ë

[lcm] rated short-circuit making capacity	80 kA at 400 V with protection by gG fuses
Breaking capacity	256 A at 400 V (AC-23B)
Short-circuit withstand	5.5 kA
Mechanical durability	20000 cycles
Electrical durability	1500 cycles AC-23A 1500 cycles AC-23B 300 cycles DC-23A 300 cycles DC-23B
Connections - terminals	Power circuit: screw-clamp terminals2.516 mm² flexible
Tightening torque	Power circuit: 3 N.m - on screw-clamp terminals

#### Environment

IEC 60947-3
CE
TH
IP20 conforming to IEC 60529 (with terminal cover)
-2070 °C
-4080 °C
960 °C body conforming to IEC 60695-2-1
98 mm
96 mm
112 mm
0.54 kg

### Offer Sustainability

REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

#### Contractual warranty

Warranty	10 months
Warrantv	18 months