



Main

Range	TeSys
Device short name	LUL
Product or component type	Communication module
Product compatibility	LUCL LUCC LUCB LUCM LUCA LUCD
Device application	Communication
Range compatibility	TeSys U LUB non reversing power base TeSys U LU2B reversing power base

Complementary

Main function available	Communication module
Mounting mode	Plug-in
Mounting location	Front side
Physical interface	RS485 multidrop
Bus type	Modbus
Cable connector type	RJ45 front panel
Communication port protocol	Modbus RTU
Addressing	0...31
Transmission rate	19200 bit/s
Return time	30 ms
Number of inputs	2
Logic input	Positive at 24 V DC - 7 mA
Response time	10 ms +/- 30 % change to state 0 10 ms +/- 30 % change to state 1
Input type	Resistive
Number of outputs	2 dedicated to starter-controller coil operation 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Us] rated supply voltage	24 V DC
Output current	<= 500 mA
Protection type	GG fuse 1 A
Switching current capacity	0.5 mA at 24 V
Local signalling	3 LEDs front panel
Connection pitch	3.81 mm
Connections - terminals	Screw clamp terminals 1 cable(s) 0.14...1 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.14...1 mm ² rigid without cable end Screw clamp terminals 1 cable(s) 0.25...0.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.25...1 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.14...0.5 mm ² rigid without cable end Screw clamp terminals 2 cable(s) 0.14...0.75 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.25...0.34 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.5 mm ² flexible with cable end
Associated cable type	AWG 26...AWG 16
Tightening torque	0.2...0.25 N.m2.5 mm
Net weight	0.08 kg

Environment

Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP20 conforming to IEC 60529

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------