

## Between Series Adaptor 33\_N-SMB-50-1/1--\_U

### Description

Adaptor plug/jack  
N plug (male) / SMB jack (female)

Interface standards  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210  
Series SMB - IEC 60169-10\_MIL-STD-348A/311\_CECC 22130



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 3 GHz ≤ 1.03 + 0.08 f (GHz)
Frequency range	3 to 4 GHz
Return loss	≥ 18 dB

#### Mechanical Data

Number of matings	500
Weight	0.0287 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - SMB jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00014303
-------------------	--------------

### Ordering Information

Single package	33_N-SMB-50-1/1--_UE
----------------	----------------------

## Between Series Adaptor

33\_N-SMB-50-1/1--\_U