



Main

Range of product	TeSys K control relay TeSys K
Range	TeSys
Device short name	LA1
Product or component type	Time delay auxiliary contact block
Pole contact composition	1 C/O
Connections - terminals	Slip-on terminals

Complementary

Mounting location	Front
[Ue] rated operational voltage	240 V AC for signalling circuit 240 V DC for signalling circuit 110...240 V AC for supply circuit
Rated operational voltage limits	0.85...1.1 U _c
[I _{th}] conventional free air thermal current	2 A
Timer type	On delay
Time delay range	1...30 s
Reset time	1.5 ms
Height	27 mm
Width	38 mm
Depth	38 mm
Net weight	0.04 kg

Environment

Environmental characteristic	Normal environment
Standards	VDE 0660 BS 5424 NF C 63-110 IEC 60947
Product certifications	UL CSA
IP degree of protection	IP2x conforming to VDE 0106

Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-10...60 °C

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------