

Connector Header

multicomp PRO


**RoHS
Compliant**

Specifications:


Pitch	: 3.5mm
Poles	: 24Poles
Housing Material	: PA 66
Pin Dimensions	: Brass, Tin Plated
PCB Hole Diameter	: 1.2mm
Operating Temperature	: -40°C to +105°C

Technical Data:

Nominal Current I_N	: 10A
Nominal Cross Section	: -
Maximum Load Current	: 10A
Insulating Material	: PA
Nominal Voltage	: 300V
Nominal Current	: 10A



Diagram



Dimensions : Millimetres (Inches)

Part Number Table

Description	Part Number
Pin Header, 3.5mm	MD023-35002
	MD023-35003
	MD023-35004
	MD023-35005
	MD023-35006
	MD023-35007
	MD023-35008
	MD023-35009
	MD023-35010
	MD023-35011

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO