EL-USB-2+

This standalone data logger measures and stores up to 16,382 relative humidity and 16,382 temperature readings over 0 to 100%RH and -35 to $+80^{\circ}$ C (-31 to $+176^{\circ}$ F) measurement ranges. The user can easily set up the logger and view downloaded data by plugging the module into a PCs USB port and using the supplied software. Relative humidity, temperature and dew point (The temperature at which water vapour present in the air begins to condense) data can then be graphed, printed and exported to other applications.

The data logger is supplied complete with a long-life lithium battery, which can typically allow logging for 1 year.

FEATURES

- Higher accuracy sensor when compared with the EL-USB-2
- 0 to 100%RH measurement range
- -35 to $+80^{\circ}$ C (-31 to $+176^{\circ}$ F) measurement range
- Dew point indication via Windows control software
- USB interface for set-up and data download
- User-programmable alarm thresholds for %RH and temperature
- Status indication via red and green LEDs
- Environmental protection to IP67
- Immediate and delayed logging
- Supplied complete with replaceable internal lithium battery and Windows control software

WINDOWS CONTROL SOFTWARE



Easy to install and use, the control software runs under Windows 2000, XP (Home and Professional Editions) and Vista (32-bit). It allows the user to set up and download data from any EL-USB product. The latest version of the control software may be downloaded from *www.lascarelectronics.com*

DATA LOGGER SETUP VARIABLES

- Logger name
- °C, °F
- Logging rate (10s, 1m, 5m, 30m, 1hr, 6hr, 12hr)
- · High and low alarms
- Immediate and delayed logging
- Data rollover (Allows unlimited logging periods by overwriting the oldest data when the memory is full)

SPECIFICATIONS

ORDERING INFORMATION

Standard Data Logger (Data Logger, Software on CD and Battery)	Stock Number EL-USB-2+
Replacement Battery	BAT 3V6

10/2008 N.J-H

Specification		Min.	Тур.	Max.	Unit
Relative Humidity	ve Humidity Measurement range	0		100	%RH
	Repeatability (short term)		±0.1		%RH
	Accuracy (overall error)		±2.0*	±4.0	%RH
	Internal resolution		0.5		%RH
	Long term stability		0.5		%RH/Yr
Temperature	Measurement range	-35 (-31)		+80 (176)	°C (°F)
	Repeatability		±0.1 (±0.2)		°C (°F)
	Accuracy (overall error)		±0.3 (±0.6)	±1.5 (±3)	°C (°F)
	Internal resolution		0.5 (1)		°C (°F)
Dew Point	Accuracy (overall error)		±1.1 (±2)**		°C (°F)
Logging rate		every 10s		every 12hr	-
Operating temperature range †		-35 (-31)		+80 (176)	°C (°F)
1/2AA 3.6V Lithium Battery Life***			1		Year

* This specifies the overall error in the logged readings for relative humidity measurements between 20 and 80%RH.

** This specifies the overall error in the calculated dew point for relative humidity measurements between 40 and 100%RH at 25°C.

*** Depending on sample rate and ambient temperature

LASCAR ELECTRONICS LTD. MODULE HOUSE WHITEPARISH WILTSHIRE SP5 2SJ UK TEL: +44 (1794) 884567 FAX: +44 (1794) 884616 E-mail: sales@lascar.co.uk LASCAR ELECTRONICS INC. 4258 West 12th Street Erie PA 16505 USA TEL: +1 (814) 835 0621 FAX: +1 (814) 838 8141 E-mail: us-sales@lascarelectronics.com LASCAR ELECTRONICS (HK) LIMITED Unit Nos. 6-8 , 19/F., Futura Plaza 111-113 How Ming Street Kwun Tong, Kowloon Hong Kong TEL: +852 2389 6502 FAX: +852 2389 6535 E-mail: saleshk@lascar.com.hk

Specifications liable to change without prior warning

ing EL-USB-2+

-2+ Issue 1

Applies to EL-USB-2+




www.lascarelectronics.com

LED FLASHING INDICATORS

EL-USB-2+

EL-USB-2+ features two bi-colour LEDs. One LED represents temperature measurement (marked by $^{\circ}$ C / $^{\circ}$ F) and the other represents relative humidity (marked by $^{\circ}$ RH). To save power, the status indication alternates between the two channels every 10 seconds i.e. The temperature channel flashes and 10 seconds later the relative humidity channel flashes, repeating for the duration of logging activity.



The number of flashes and colours indicate:

0	(Single LED, Single Flash)	The channel is logging, no alarm
((Single LED, Double flash)	Delayed start
\bigcirc	(Single LED, Triple flash)	Logger full, no alarm
/		
0	(Single LED, Single Flash)	The channel is logging, low alarm
—	(Single LED, Double flash)	The channel is logging, high alarm
///	(Single LED, Triple flash)	Logger full, alarm

Specifications liable to change without prior warning

EL-USB-2+

Issue 1

10/2008 N.J-H



www.lascarelectronics.com

Page 2 of 4

EL-USB-2+

LEDs	Meaning	Action
	No LEDs flash	Start logging.
	 No logging started. or Battery fitted buy completely discharged. 	Replace battery.
RH T OO	or - No battery fitted.	Fit battery, start logging.
	Plug the data logger into the PC and run the control software to find out which condition applied.	
RH T	Alternating green double flash every 10 seconds	
Repeating sequentially	- Logger configured for delayed start.	No action needed, logger will start at a later date and time.
	Alternating greens single flash every 10 seconds	
	 Logger operating. Last stored Humidity and Temperature readings within set alarm levels. (If hold is enabled, then a flashing Green LED indicates that no alarm condition has ever been logged). 	None.
$\begin{array}{c} \mathbf{R}\mathbf{H} \mathbf{T} \qquad \mathbf{R}\mathbf{H} \mathbf{T} \\ () 10s \qquad () 10s \\ \mathbf{O} \mathbf{O} \mathbf{O} \end{array}$	Alternating between green and red single flash every 10 seconds	
	 The green LED indicates the parameter that is within set alarm levels. The red LED indicates the parameter for which the Low alarm level has been exceeded. (If hold is enabled, then the alarm condition may have been triggered at any point during the current logging session). 	
RHT RHT	Alternating between single green and double red flash every 10 seconds	
$ \begin{array}{c} & & & & \\ () \\ () \\ 10s \\ () \\ 10s \\ () \\ 10s \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\$	 The green LED indicates the parameter that is within set alarm levels. The red LED indicates the parameter for which the high alarm level has been exceeded. (If hold is enabled, then the alarm condition may have been triggered at any point during the current logging session). 	
RH T RH T RH T RH T	Alternating between green or red triple flash every 10 seconds	
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	Warning : Logger memory is full. In this condition, hold is automatically enabled, and a flashing Green LED	Download Data.
$\begin{array}{c} \circ \circ$	indicates that no alarm condition has ever been logged. A Red LED indicates that an alarm condition has been logger.	
RH T	Simultaneous red single flash every 60 seconds	
()60s	Warning : Battery is nearly discharged.	
è é	No alarm conditions are indicated.	Fit new battery and download data.
	Once the battery is exhausted, no LEDs will flash.	

Specifications liable to change without prior warning


EL-USB-2+

Issue 1

10/2008 N.J-H



www.lascarelectronics.com



CAUTION

Exposure of the internal sensor to chemical vapours such as those produced by some plastics and foamed materials may interfere with the internal sensor and cause inaccurate readings to be logged. In a clean environment, this will slowly rectify itself, therefore ensure that the logger is used in a ventilated area i.e. air exchange is allowed.

Exposure to extreme conditions or chemical vapours will require the following reconditioning procedure to bring the internal sensor back to calibration state. 80° C (176°F) at <5% RH for 36h (baking) followed by 20-30°C (70-90°F) at >74% RH for 48h (re-hydration).

High levels of pollutants may cause permanent damage to the internal sensor.

Specifications liable to change without prior warning

EL-USB-2+

Issue 1

10/2008 N.J-H



www.lascarelectronics.com