



Mallory Sonalert Products, Inc.

Part #:

MSS5GL

Sales Outline Drawing

Revision:

A


Specifications:	cUL Recognized to IEC60601-1-8 Any Melody - Low Priority	
Sound Level Category:	Loud	
Mode of Operation:	Low Priority Alarm	2 beeps repeating every 30 sec
Voltage Rating:	5 ± 0.5 VDC	
Loudness @ 10cm:	85 to 95 dB(A) Typ.	
Frequency:	150 to 4000 Hz	
Average Current Draw:	<200mA Typ.	
Ipk Current*:	400mA	
Housing Material:	Valox (UL94V-0), Color: Black	
Storage Temperature:	-30° to +60° C	
Operating Temperature:	-30° to +55° C	
Weight Typical:	6.0g	
Options:	Please contact factory.	

Dimensions: Inches (mm)



cUL Recognized

ROHS Compliant

PATENT NUMBER: 7880593



EMISSION HOLE



NOTE A:
TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:
MOUNTING- INSERT INTO PRINTED CIRCUIT BOARD AND HAND OR MACHINE SOLDER.
UNITS ARE SUITABLE FOR WAVE SOLDERING. BOARDS ARE NOT SUITABLE FOR WASH.
RECOMMENDED MAXIMUM TEMPERATURE AND TIME DURATION FOR WAVE SOLDERING IS
+270°C AND 3 SECONDS RESPECTIVELY.

*Ipk = Instantaneous Peak