



AMP

TE Internal #: 2151018-1

Applicators, Mechanical Feed, OCEAN, Male Adapter Post - Atlantic Style Application Interface

[View on TE.com >](#)

Application Tooling > Applicators



Feed Type: **Mechanical**

Applicator & Product Style: **OCEAN**

Application Interface: **Male Adapter Post - Atlantic Style**

Service Options: **Capability Study, Crimped Samples, Cross Section - Photograph**

Terminator Type: **30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator**

Features

Other

Feed Type	Mechanical
Applicator & Product Style	OCEAN
Application Interface	Male Adapter Post - Atlantic Style
Service Options	Capability Study, Crimped Samples, Cross Section - Photograph
Terminator Type	30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator
Alignment Aids	Alignment Gauge, Camera

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205)



Candidate List Declared Against: JUN 2018 (191)

Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # 2298107-3
DYNAMIC D-3 FMLB REC CONT AU0.38 L SIZE



TE Model / Part # 175286-2
DYNAMIC D-3 TAB CONT. L AU 0.38



TE Model / Part # 175196-3
DYNAMIC D-3 REC CONT/L AU 0.76



TE Model / Part # 175286-3
DYNAMIC D-3 TAB CONT. L AU 0.76



TE Model / Part # 175286-5
DYNAMIC D-3 TAB CONT. L PRE-TIN



TE Model / Part # 1-175196-5
DYNAMIC D-3 REC CONT/L PRE-TIN



TE Model / Part # 175196-2
DYNAMIC D-3 REC CONT. L AU 0.38



TE Model / Part # 2161400-5
AMP 3K/40 CE EL TERMINATOR



TE Model / Part # 2161700-4
SK CE STRIPPING MODULE



TE Model / Part # 2161700-5
SK CE STRIPPING MODULE W/ CQM




TE Model / Part # 2217001-3
MODEL G II STRIPPING MODULE



TE Model / Part # 2217001-4
MODEL G II STRIPPING MODULE W /CQM



TE Model / Part # 3-2161500-1
AMP 5K/30 CE TERMINATOR



TE Model / Part # 7-2151018-7
OCEAN_2.0_SPARE_PART_KIT-090F110F



TE Model / Part # 2217000-2
MODEL G II CE TERMINATOR, W /CQM



TE Model / Part # 2161500-1
AMP 5K/40 CE TERMINATOR



TE Model / Part # 1803095-1
FLOATING SHEAR, FRONT



TE Model / Part # 2217000-1
G II CE TERMINATOR



TE Model / Part # 1803095-6
FLOATING SHEAR, FRONT



TE Model / Part # 2119805-1
SHEAR HOLDER, FRONT, CUT

Customers Also Bought



TE Model / Part #7-2151018-7
OCEAN_2.0_SPARE_PART_KIT-090F110F



TE Model / Part #5-456406-6
CRIMPER, WIRE .090 "F"



TE Model / Part #4-1333205-8
ANVIL, COMBINATION .090



TE Model / Part #1-178708-9
PL EX SLEEVE 187 FLAG BLACK 6/6 NYLON



TE Model / Part #172890-2
2P 2MM MINI AMP-IN HDR HSG



TE Model / Part #172890-5
5P 2MM MINI AMP-IN HDR HSG



TE Model / Part #172890-6
6P 2MM MINI AMP-IN HDR HSG



TE Model / Part #2151080-1
OCEAN_2.0_APPLICATION-S-062F110F



Documents

Product Drawings

[OCEAN_2.0_APPLICATOR-S-090F110F](#)

English

Datasheets & Catalog Pages

[TE_APPLICATORS_CATALOG](#)

English

[1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English