

601967-1 ✓ ACTIVE

AMP

TE Internal #: 601967-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,
Not Adjustable, Fixed In Tool, MIL Spec, Pneumatic / Manual, Four
Indent Hand Tool

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **MIL Spec**

Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - 4 Indent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec
Certification	Upon Request for Fee
Power Type	Manual, Pneumatic
Tool Type	Four Indent Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JAN 2020
(205)

Candidate List Declared Against: JAN 2018
(181)

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts






TE Model / Part # CAT-AM71-C83998K
CPC SERIES 6



TE Model / Part # CAT-M1-P489C
M12 CRIMP CONTACT FOR D AND A5



TE Model / Part # CAT-AM71-T98
TYPE II CONTACTS



TE Model / Part # CAT-AM71-T98A
TYPE III CONTACTS LP



TE Model / Part # 208273-2
SKT ASSY, SZ 12



TE Model / Part # 1766195-1
CONTACT,PIN,SIZE #12



TE Model / Part # 208271-3
PIN CONT, SZ 12



TE Model / Part # 1650161-1
701-64-02109=CONTACT,PIN,#20



TE Model / Part # 1648203-1
297-08-01100=SA CONN,PIN



TE Model / Part # 1648206-1
298-08-01100=SA CONN,SKT



TE Model / Part # 204219-1
PIN CONTACT ASSY.




TE Model / Part # 1648325-1
702-92-01109=CONTACT,SKT,#20

Customers Also Bought




TE Model / Part #200893-2
INSERTION TOOL CONT



TE Model / Part #601966-5
K13-1 POSITIONER



TE Model / Part #601966-1
CRIMPING TOOL M22520/2-01



TE Model / Part #69710-1
SAHT W/OUT DIES



TE Model / Part #1757823-7
AMPLIMITE,ASY,PLUG,STD,90,ZN,1,CT



TE Model / Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1,CT



TE Model / Part #1648325-1
702-92-01109=CONTACT,SKT,#20



TE Model / Part #1757820-6
AMPLIMITE,ASY,RCPT,STD,109,ZN,1,CT



Documents

Datasheets & Catalog Pages

Signal Contacts

English

AMP Circular Connectors for Commercial Signal & Power Applications

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Instruction Sheets

Instruction Sheet (U.S.)

English