

FAIRCHILD

© 1998 Fairchild Semiconductor Corporation DS006177

www.fairchildsemi.com

DM74ALS04B Hex Inverter

February 1998

Absolute	Maximum	Ratings (Note 1)
----------	---------	------------------

Supply Voltage	7V
Input Voltage	7V
Operating Free Air Temperature Range DM74ALS	0°C to +70°C

Storage Temperature Range	–65°C to +150°C
Typical θ _{JA}	
N Package	88.0°C/W
M Package	118.5°C/W

Recommended Operating Conditions

Symbol	Parameter		DM74ALS04B		
		Min	Nom	Max]
V _{cc}	Supply Voltage	4.5	5	5.5	V
V _{IH}	High Level Input Voltage	2			V
VIL	Low Level Input Voltage			0.8	V
I _{он}	High Level Output Current			-0.4	mA
I _{OL}	Low Level Output Current			8	mA
T _A	Free Air Operating Temperature	0		70	°C

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Electrical Characteristics

over recommended operating free air temperature range. All typical values are measured at V_{CC} = 5V, T_A = 25°C.


Symbol	Parameter	Conditions		Min	Тур	Max	Units
V _{IK}	Input Clamp Voltage	$V_{\rm CC}$ = 4.5V, I ₁	$V_{\rm CC}$ = 4.5V, I _I = -18 mA			-1.2	V
V _{он}	High Level Output	I _{OH} = -0.4 mA	$I_{OH} = -0.4 \text{ mA}$				V
	Voltage	$V_{\rm CC}$ = 4.5V to	$V_{\rm CC}$ = 4.5V to 5.5V				
V _{OL}	Low Level Output	$V_{\rm CC} = 4.5V$	74ALS		0.35	0.5	V
	Voltage		I _{OL} = 8 mA				
I _I	Input Current @ Max.	V _{CC} = 5.5V, V _I	$V_{CC} = 5.5V, V_{IH} = 7V$			0.1	mA
	Input Voltage						
I _{IH}	High Level Input Current	V _{CC} = 5.5V, V _I	V _{CC} = 5.5V, V _{IH} = 2.7V			20	μA
I _{IL}	Low Level Input Current	V _{CC} = 5.5V, V _I	$V_{\rm CC} = 5.5 V, V_{\rm IL} = 0.4 V$			-0.1	mA
lo	Output Drive Current	$V_{\rm CC} = 5.5V$	V _O = 2.25V	-30		-112	mA
I _{cc}	Supply Current	V _{CC} = 5.5V	Outputs High		0.65	1.1	mA
			Outputs Low		2.4	4.2	mA

Switching Characteristics (Note 2) over recommended operating free air temperature range


Symbol	Parameter	Conditions	DM74ALS04B		Units
			Min	Max	1
t _{PLH}	Propagation Delay Time	$V_{CC} = 4.5V$ to 5.5V	3	11	ns
	Low to High Level Output	$R_L = 500\Omega$			
t _{PHL}	Propagation Delay Time	C _L = 50 pF	2	8	ns
	High to Low Level Output				

Note 2: See Section 1 for test waveforms and output load.

www.fairchildsemi.com



www.fairchildsemi.com



Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.