

Inductors for power circuits **Wound ferrite VLS-CX-1** series









VLS3010CX-1 type
















FEATURES

- OMagnetic shield type wound inductor for power circuits using a ferrite magnetic material.
- O High magnetic shield construction and compatible with high-density mounting.
- O Larger current and lower Rdc were achieved by optimizing the ferrite core figure.
- Operating temperature range: -40 to +105°C (including self-temperature rise)

APPLICATION

O Smart phones, tablet terminals, HDDs, SSDs, DVCs, DSCs, mobile display panels, portable game devices, compact power supply modules, other

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

L		Measuring frequency	DC resista	ance	Rated cur	rent*			Part No.
(μH)	Tolerance	(MHz)	(Ω)max.	(Ω)typ.	Isat (A)max.	Isat (A)typ.	Itemp (A)max.	Itemp (A)typ.	
1.0	±20%	1	0.047	0.039	1.76	1.95	3.20	3.55	VLS3010CX-1R0M-1
1.5	±20%	1	0.059	0.049	1.44	1.60	2.74	3.05	VLS3010CX-1R5M-1
2.2	±20%	1	0.078	0.065	1.11	1.23	2.19	2.43	VLS3010CX-2R2M-1
3.3	±20%	1	0.100	0.083	0.90	1.00	2.09	2.32	VLS3010CX-3R3M-1
4.7	±20%	1	0.145	0.121	0.78	0.87	1.68	1.86	VLS3010CX-4R7M-1
6.8	±20%	1	0.179	0.149	0.64	0.71	1.52	1.69	VLS3010CX-6R8M-1
10	±20%	1	0.302	0.252	0.50	0.56	1.10	1.22	VLS3010CX-100M-1
15	±20%	1	0.427	0.356	0.44	0.49	0.86	0.96	<u>VLS3010CX-150M-1</u>
22	±20%	1	0.624	0.520	0.33	0.37	0.77	0.86	VLS3010CX-220M-1
33	±20%	1	0.876	0.730	0.25	0.28	0.68	0.75	VLS3010CX-330M-1
47	±20%	1	1.392	1.160	0.23	0.25	0.50	0.55	<u>VLS3010CX-470M-1</u>
68	±20%	1	1.992	1.660	0.17	0.19	0.37	0.42	<u>VLS3010CX-680M-1</u>
100	±20%	1	2.988	2.490	0.15	0.17	0.30	0.34	VLS3010CX-101M-1

^{*} Rated current: smaller value of either Isat or Itemp.

Isat: When based on the inductance change rate (30% below the initial L value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Measurement equipment

Measurement item	Product No.	Manufacturer
L	4294A	Keysight Technologies
DC resistance	34420A	Hewlett-Packard
Rated current Isat	4285A+42841A+42842C	Keysight Technologies

^{*} Equivalent measurement equipment may be used.








VLS3010CX-1 type

L FREQUENCY CHARACTERISTICS




Measurement equipment

Product No.	Manufacturer
4294A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

■INDUCTANCE VS. DC BIAS CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
4285A+42841A+42842C	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



VLS3010CX-1 type


SHAPE & DIMENSIONS




Dimensions in mm

PACKAGING STYLE


REEL DIMENSIONS






Dimensions in mm

■ RECOMMENDED LAND PATTERN



Dimensions in mm


TAPE DIMENSIONS



Dimensions in mm

Туре	Α	В	K
VLS3010CX-1	3.3±0.1	3.3±0.1	1.15±0.1

■ RECOMMENDED REFLOW PROFILE



□PACKAGE QUANTITY

Package quantity	2000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating	Storage	Individual	
temperature range*	temperature range**	weight	
–40 to 105 °C	–40 to 105 °C	35 mg	

^{*} Operating temperature range includes self-temperature rise.

^{**} The storage temperature range is for after the assembly.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

⚠ REMINDERS
storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 30°C, humidity: 10 to 75% RH of the storage period elapses, the soldering of the terminal electrodes may deteriorate.
ot use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
re soldering, be sure to preheat components. preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature and chip temperature and chip temperature.
ering corrections after mounting should be within the range of the conditions determined in the specifications. erheated, a short circuit, performance deterioration, or lifespan shortening may occur.
n embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermagn.
fully lay out the coil for the circuit board design of the non-magnetic shield type. alfunction may occur due to magnetic interference.
a wrist band to discharge static electricity in your body through the grounding wire.
ot expose the products to magnets or magnetic fields.
ot use for a purpose outside of the contents regulated in the delivery specifications.
products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equip t, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equip t, industrial robots) under a normal operation and use condition. products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or qual equire a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment

person or property.

(4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions