

Product availability : Stock - Normally stocked in distribution facility



Price** : 589.00 USD



Main

Range of product	OsiSense XX
Sensor type	Ultrasonic sensor
Sensor name	XX9
Material	PBT (polybutylene terephthalate)
Sensor design	Ø 30 mm
Product specific application	Analog output
Type of output signal	Analogue
Wiring technique	4 wires
[Us] rated supply voltage	15...24 V DC reverse polarity protection
Electrical connection	1 male connector M12 4 pins
[Sd] sensing range	0.17...0.33 ft (0.051...0.1 m)
Beam angle	10 °
IP degree of protection	IP67 IEC 60529

Complementary

Enclosure material	ULTEM
Front material	Silicone
ISO thread	M30 x 1.5
Supply voltage limits	10...28 V DC
Analogue output range	4...20 mA direct
[Sn] nominal sensing distance	3.28 ft (1 m)
Type of sensing window	Adjustable
[Sa] assured operating distance	0.17...3.25 ft (0.051...0.991 m) teach mode)
Maximum differential travel	0.10 in (2.5 mm)
Blind zone	2.01 in (51 mm)
Transmission frequency	200 kHz
Repeat accuracy	0.9 %

Deviation angle from 90° of object to be detected	-8...8 °
Minimum size of detected object	Cylinder diameter 1.6 mm - up to 635 mm sensing distance
Status LED	Output state 2 LEDs green/red (flashing) Setting-up assistance 2 LEDs green/red (flashing) Distance indication 2 LEDs yellow
Current consumption	100 mA
Maximum switching current	100 mA overload and short-circuit protection
Maximum switching capacity	10...500 Ohm overload and short-circuit protection
Maximum delay first up	1200 ms
Maximum delay response	25 ms
Maximum delay recovery	1000 ms
Marking	CE
Maximum Height	1.18 in (30 mm)
Maximum Width	1.18 in (30 mm)
Maximum Depth	1.18 in (30 mm)
Length	3.78 in (96 mm)
CAD overall height	3.78 in (95.99 mm)
CAD overall width	1.35 in (34.17 mm)
CAD overall depth	1.35 in (34.17 mm)
Net Weight	0.20 lb(US) (0.09 kg)

Environment

Standards	IEC 60947-5-2
Product certifications	UL
NEMA degree of protection	NEMA 4X indoor use only)
Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 4 IEC 61000-4-2
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	00785901353485
Package weight(Lbs)	0.09 lb(US) (0.04 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------
