

PRODUCT-DETAILS

S20/10M

10M X S20 CONDUIT



General Information

Extended Product Type	S20/10M
Product ID	7TCA296010R0057
EAN	5020963000584
Catalog Description	10M X S20 CONDUIT
Long Description	Inherent Low Fire Hazard Steel Conduit, Nominal Conduit Size 20mm, Outside Diameter 20.5mm, Inside Diameter 16.9mm, Static Bend Radius 45mm, Reel Length 10 Meters, Galvanised Steel General Purpose

Ordering

EAN	5020963000584
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	5.19 lb 2.354 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	17 in 432 mm

Package Level 2 Height	16 in 406 mm
Package Level 2 Depth / Length	16 in 406 mm

Additional Information

Application	Indoors / Outdoors - Light Industrial, Buildings
Brand / Label	Adaptaflex
Flexibility	Very High
Inside Diameter	16.9 mm
Material	Galvanized Steel
Nominal Size	1/2 in
Number of Batteries	0
Outside Diameter	20.5 mm
Product Name	STEEL CONDUIT
Product Type	Low Fire Hazard Conduit
Radius	45 mm
Special Functions	Very High UV Protection and Fatigue Life
UPC	786210260594

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	S20/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	S20/10M

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

