

PRODUCT-DETAILS

# S25/10M

## 10M X S25 CONDUIT



### General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | S25/10M  |
| Product ID            | 7TCA296010R0086  |
| EAN                   | 5020963001468  |
| Catalog Description   | 10M X S25 CONDUIT  |
| Long Description      | Inherent Low Fire Hazard Steel Conduit, Nominal Conduit Size 25mm, Outside Diameter 25.0mm, Inside Diameter 21.4mm, Static Bend Radius 55mm, Reel Length 10 Meters, Galvanised Steel General Purpose |

### Ordering

|                       |               |
|-----------------------|---------------|
| EAN                   | 5020963001468 |
| Customs Tariff Number | 8307106000    |

### Dimensions

|                    |                     |
|--------------------|---------------------|
| Product Net Weight | 6.17 lb<br>2.798 kg |
|--------------------|---------------------|

### Container Information

|                       |               |
|-----------------------|---------------|
| Package Level 2 Units | 1 piece       |
| Package Level 2 Width | 1 in<br>25 mm |

|                                |               |
|--------------------------------|---------------|
| Package Level 2 Height         | 1 in<br>25 mm |
| Package Level 2 Depth / Length | 1 in<br>25 mm |

---

## Additional Information

|                     |  |
|---------------------|--|
| Application         | Indoors / Outdoors - Light Industrial, Buildings |
| Brand / Label       | Adaptaflex                                       |
| Flexibility         | Very High  |
| Inside Diameter     | 21.4 mm  |
| Material            | Galvanized Steel                                 |
| Nominal Size        | 3/4 in   |
| Number of Batteries | 0  |
| Outside Diameter    | 25.0 mm  |
| Product Name        | flex metal conduit                               |
| Product Type        | Low Fire Hazard Conduit                          |
| Radius              | 55 mm  |
| Special Functions   | Very High UV Protection and Fatigue Life         |
| UPC                 | 786210251462                                     |

---

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | S25/10M         |
| Declaration of Conformity - CE    | 9AKK107492A9618 |
| Instructions and Manuals          | S25/10M         |

---

## Classifications

|                                    |                                     |
|------------------------------------|-------------------------------------|
| ETIM 6                             | EC001179 - Protective metallic hose |
| ETIM 7                             | EC001179 - Protective metallic hose |
| UNSPSC                             | 39131706                            |
| WEEE Category                      | Product Not in WEEE Scope           |
| IDEA Granular Category Code (IGCC) | 5535 >> Electrical conduit          |

---

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

