

PRODUCT-DETAILS

XQM0606

KFF STR CONNECTORS 32X32MM



Product image
not available

General Information

Extended Product Type	XQM0606
Product ID	7TCA297020R0493
EAN	5011949209589
Catalog Description	KFF STR CONNECTORS 32X32MM
Long Description	Liquid Tight Fitting for Covered Conduit, Straight with External Male Thread, Conduit Size 32mm, M32 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Nickel Plated Brass with a Co-Polyester Seal and Nylon Insert

Ordering

EAN	5011949209589
Customs Tariff Number	7412200090

Dimensions

Product Net Weight	.31 lb 140.59 g
--------------------	--------------------

Container Information

Package Level 2 Units	5 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	For Insertion Into Threaded Entries & Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass with a Co-Polyester Seal and Nylon Insert
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Straight Fitting with External Thread for Covered Conduit
Size	Conduit Size 32mm ; M32 Thread
Special Functions	Very High UV Protection and Mechanical Protection
Standards	UL E60625, BSI Kitemark KM-90009, Low Voltage Directive
Surface Finishing	Nickel Plated
UPC	786210253985

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	XQM0606
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	XQM0606

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available