
PRODUCT-DETAILS

EXLB0510

FLEX CONDUIT 25MM OIL RESISTANT 10M



General Information

Extended Product Type	EXLB0510
Product ID	7TCA297120R0073
EAN	5011949001145
Catalog Description	FLEX CONDUIT 25MM OIL RESISTANT 10M
Long Description	Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 25mm, Minimum Bore 21mm, Reel Length 10 Meters, Galvanised Steel Core with Flame Retardant PVC Covering, Black

Ordering

EAN	5011949001145
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	11.4 lb 5.17 kg
--------------------	--------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Connection for Conduit Systems when Oil and Acid Resistance is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	21 mm
Material	Galvanized Steel Core with Flame Retardant PVC Covering
Nominal Size	25 mm
Number of Batteries	0
Product Name	flexible metal conduit
Product Type	Liquid Tight Metallic Conduit
Special Functions	Flame Retardant PVC Covering
Standards	IEC 61386
UPC	786210287423

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLB0510
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLB0510

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

