



## Rollatape POLYCLOTH LAMINATE

- HIGH TACK

Colours - Black, White and Silver



Technical Data

TECHNICAL

DATA SHEET

Typical values

**Thickness** 

0.21mm

Breaking Load

30N/cm

Elongation

10%

**Applications** 

sensitive adhesive.

Description

ideal for sealing and bundling within the HEVAC and construction industries.

laminated polythene cloth tape with a very aggressive pressure

Adhesion

Steel Self

7.0N/cm 2.3N/cm

Moisture Vapour Permeability

25g/m<sup>2</sup>/24hrs

Service Temp

-50°C to 65°C

Application Temp

0°C to 40°C

Note

Except where indicated otherwise, the above figures are average values and should not Except where indicated otherwise, the above figures are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The company reserve the right to improve products and any change in specification will company reserve the televant 'Technical Data' sheet. Customers should satisfy result in a re-issue of the relevant 'Technical Data' sheet. Please check that you have the latest issue of the modifications or otherwise. Please check that you have the latest issue of the modifications or otherwise. All slitting and length tolerances are to British Standards, but other tolerances are available by request. Before use the customer is advised to consult the Health & Data sheet produced by the company for this product, which is available on request. This product is not recommended for gas fire back plate closure. Use AT293 Premier Closure Plate Tape.

Storage
Tapes stored below the minimum application temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

## 24 Hour Technical Service Hotline 0116 265 1210 · Fax: 0116 265 3070







ADVANCE TAPES INTERNATIONAL LTD., P.O. BOX 122, LEICESTER LE4 5RA TELEPHONE: 0116 251 0191 · FAX: 0116 265 2046

