Note: This datasheet may be out of date. Please download the latest datasheet of 1277AS-H-4R7M# from the official website of Murata Manufacturing

### 1277AS-H-4R7M#

"#" indicates a package specification code.













< List of part numbers with package codes > 1277AS-H-4R7M=P2




# Appearance & Shape



#### References





(in mm)

Packaging	Specifications	Minimum Order Quantity
=P2	180Embossed Tape	3000

Mass (	(typ.)	
1 piec	e	0.0448g



Rated current (Isat) is specified when the decrease of the initial inductance value at 30%. Rated current (Itemp) is specified when temperature of the inductor is raised 40°C by DC current.

1 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date. Please download the latest datasheet of 1277AS-H-4R7M# from the official website of Murata Manufacturing Co., Ltd.

# 1277AS-H-4R7M#

"#" indicates a package specification code.



L size	3.2±0.2mm
W size	2.5±0.2mm
T size	1.2mm
Size code inch (mm)	1210 (3225)
Inductance	4.7μH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	1800mA
Rated current (Itemp) (Based on Temperature rise)	1400mA
Max. of DC resistance	0.18Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 85°C
Class of magnetic shield	Metal Alloy
Absolute maximum voltage	20Vdc
Series	DFE322512C

2 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




http://www.murata.com/en/products/productdetail?partno=1277AS-H-4R7M%


### 1277AS-H-4R7M#

"#" indicates a package specification code.





The charts below may show another part number which shares its characteristics.











3 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


 $2. This \ data{sheet has only typical specifications because there is no space for \ detailed \ specifications.}$ 

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



# 1277AS-H-4R7M#

"#" indicates a package specification code.



4 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

