

Product Search Data Sheet

Note: This datasheet may be out of date. Please Jownload the latest datasheet of LQH31HNR88J03# from the official website of Murata Manufacturing Co., Ltd.

ata.com/en/products/productdetail?partno=LQH31HNR88J03%23

## LQH31HNR88J03#

"#" indicates a package specification code.


#### Size Code 3216 (1206) in mm (in inch), Ferrite Core High Frequency Wound Type



< List of part numbers with package codes > LQH31HNR88J03K LQH31HNR88J03L

# Appearance & Shape





(in mm)

0.7 min.



Packaging	Specifications	Minimum Order Quantity
K	330Embossed Tape	7500
L	180Embossed Tape	2000

0.7 min

Mass (typ.)	
1 piece	0.029g

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of LQH31HNR88J03# from the official website of Murata Manufacturing Co., Ltd. http://www.n nurata.com/en/products/productdetail?partno=LQH31HNR88J03%23

LQH31HNR88J03#

"#" indicates a package specification code.

## Specifications

L size	3.2±0.3mm
W size	1.6±0.2mm
T size	1.8±0.2mm
Size code inch (mm)	1206 (3216)
Inductance	880nH±5%
Inductance Test Frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	180mA
Max. of DC resistance	1.118Ω
Q(min.)	60
Q Test Frequency	100MHz
Self resonance frequency (min.)	200MHz
Operating Temperature Range(Self- temperature rise is not included)	-40°C to 85°C
DC Resistance Intermediate Values	0.86Ω±30%
Series	LQH31HN_03

2 of 3

This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Attention




Product Search Data Sheet

Note: This datasheet may be out of date Please download the latest datasheet of LQH31HNR88J03# from the official website of Murata Manufacturing Co., Ltd. http:/ ata.com/en/products/productdetail?partno=LQH31HNR88J03%23

### LQH31HNR88J03#

"#" indicates a package specification code.





Q-Frequency Characteristics

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Attention