

# RL73N1JR10JTD ✓ ACTIVE

CGS | CGS RL73

TE Internal #: 6-1622824-1

CGS RL73, Surface Mount Resistors, Current Sensing Resistor, 2 Terminations, Size Code 0603, Taped & Reeled, 5%, Thick Film

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Current Sensing Resistor**

Number of Terminations: **2**

Size Code: **0603**

Packaging Method: **Taped & Reeled**

Tolerance: **5%**

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Current Sensing Resistor
Size Code	0603
Element Type	Thick Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Tolerance	5%
Resistance Range	Up to 1k $\Omega$
Resistance	.1 $\Omega$
Power Rating	.1 W

### Termination Features

Number of Terminations	2
Termination Type	Solder

### Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

### Dimensions

Dimensions	1.6 x .8 x .45 mm
------------	-------------------

### Usage Conditions

Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205)
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



TE Model / Part # 1879463-6  
RL73H 2E R16 1% 5K RL



TE Model / Part # 1-1879463-8  
RL73H 2E R51 1% 5K RL



TE Model / Part # 1879463-4  
RL73H 2E R13 1% 5K RL



TE Model / Part # 2-1879464-9  
RL73H 2H R18 1% 1K RL



TE Model / Part # 4-1879463-3  
RL73H 2E R56 1% 1K RL



TE Model / Part # 4-1622824-9  
RL73H 3A R12 1% 1K RL



TE Model / Part # 2-1879461-4  
RL73H 2A R12 1% 1K RL



TE Model / Part # 3-1879463-4  
RL73H 2E R24 1% 1K RL



TE Model / Part # 1-1879463-1  
RL73H 2E R27 1% 5K RL



TE Model / Part # 3-1879463-6  
RL73H 2E R30 1% 1K RL



TE Model / Part # 3-1879463-9  
RL73H 2E R39 1% 1K RL



TE Model / Part # 1-1879463-9  
RL73H 2E R56 1% 5K RL



TE Model / Part # 5-1622825-1  
RL73K 3A R68 5% 4K RL



TE Model / Part # 5-1622824-4  
RL73N 1E R27 5% 5K RL



TE Model / Part # 1879463-7  
RL73H 2E R18 1% 5K RL



TE Model / Part # 8-1622824-5  
RL73H 3A R30 1% 1K RL



TE Model / Part # 1-1622824-4  
RL73H 3A R22 1% 4K RL



TE Model / Part # 8-1622824-4  
RL73H 3A R27 1% 1K RL




TE Model / Part # 2-1879460-5  
RL73N 1J R10 1% 1K RL



TE Model / Part # 2-1879464-8  
RL73H 2H R16 1% 1K RL

Also in the Series | **CGS RL73**



Surface Mount Resistors(856)

## Customers Also Bought



TE Model / Part #440055-4  
2.0MM,HDR,4POS,R/A




TE Model / Part #969973-5  
2x5P HV100 REC. CON, SMD, GOLD, BLISTER



TE Model / Part #1-1879208-3  
CPF 0402 33R 0.1% 25PPM 1K RL



TE Model / Part #2176050-8  
RLP73N 1E R10 5% 5K RL



TE Model / Part #84953-6  
1MM FPC HORZ.TOP CONT.ASSY 6P



TE Model / Part #9-1879333-1  
CPF0402 200K 0.1% 25PPM 5K RL



TE Model / Part #1734742-6  
.5 FPC VT ZIF Type-A 6 CONT



TE Model / Part #440055-2  
2.0MM,HDR,2POS,R/A



TE Model / Part #5650478-5  
ASSY,PIN,EUROCARD,TYPE C/2,LEA

## Documents

### Product Drawings

[RL73N 1J R10 5% 5K RL](#)

English

### CAD Files

[3D PDF](#)

[3D](#)

### Customer View Model

[ENG\\_CVM\\_CVM\\_6-1622824-1\\_BA.2d\\_dxf.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_6-1622824-1\\_BA.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_6-1622824-1\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[SMD Low Ohmic Current Sense Resistors - Type RL73 Series](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English

[Standard Tantalum Capacitors - Type TYTS Series - Tyco Electronics Passives](#)

English