

SMF2560RJT ✓ ACTIVE

CGS | CGS SM

TE Internal #: 1-1879011-1

CGS SM, Surface Mount Resistors, Power Resistor, 2 Terminations, Taped & Reeled, 5%, Metal Film, Resistance Range Up to 1kΩ Ω, 560 Resistance

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**

Number of Terminations: **2**

Packaging Method: **Taped & Reeled**

Tolerance: **5%**

Element Type: **Metal Film**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	300 V
Tolerance	5%
Resistance Range	Up to 1kΩ Ω
Resistance	560 Ω
Power Rating	2 W

Termination Features

Number of Terminations	2
Termination Type	Solder

Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

Dimensions

Dimensions	6.7 x 4 x 3.55 mm
------------	-------------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




Also in the Series | **CGS SM**






RJ45 Connectors(3)



SD Card Connectors(1)



Surface Mount Resistors(369)

Customers Also Bought



TE Model / Part #2057042-1
1x3 QSFP Kit Assy LP&HS, PCI



TE Model / Part #1-1879011-3
SMF2 680R 5%



TE Model / Part #1-1879011-5
SMF2 820R 5%



TE Model / Part #1879011-9
SMF2 470R 5%



TE Model / Part #6-1624112-4
3650 0603 3.9nH 5% 2K RL



TE Model / Part #6-1393250-4
W28-XT1A-12=W28




TE Model / Part #3-828102-1
HD-20SCHRAUB-SICHRG



TE Model / Part #4-1625875-3
CBT 1/4 5% 6R8



TE Model / Part #4-1624112-4
3650 0402 16nH 5% 2K RL



TE Model / Part #6-1879663-9
H8 549R 0.1% 15PPM

Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_1-1879011-1_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1879011-1_BA.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1-1879011-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English

[SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives](#)

English