

# Pan head machine screws

Slotted

### Dimensions

DIN 85


BS 4183

ISO 1580

Materials / Finishes:

Stainless steel / Self colour

Other materials and finishes available on request



d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
D max	4	5	6	7	8	10	12	16
H max	1.3	1.5	1.8	2.1	2.4	3	3.6	4.8
w (slot width) nom	0.7	0.8	1	1.2	1.4	1.5	1.8	2.2
t (slot dpth) nom	0.5	0.6	0.7	0.8	1	1.2	1.4	1.9

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

### Preferred sizes - Stainless steel

d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
L	5			TP				
	6		TP	TP		TP		
	8		TP	TP		TP	TP	
	10		TP	TP		TP	TP	TP
	12		TP	TP		TP	TP	TP
	16			TP		TP	TP	TP
	20			TP		TP	TP	TP
	25				TP	TP	TP	
	30				TP	TP	TP	
	35				TP	TP	TP	
	40							
	45							
	50							
	60							
	65							
	70							