



“TIGER TAIL” LOCKNUT:




THREAD TYPE	ORDERING CODE	DIMENSIONS (mm)	
		LUG DIAMETER	THICKNESS
1/2" NPT	WHAS04	28.5	5.3
3/4" NPT	WHAS05	33.5	6.0
1" NPT	WHAS06	43.5	6.0
1.1/4" NPT	WHAS07	52.2	6.0
1.1/2" NPT	WHAS08	60.3	5.8
2" NPT	WHAS09	73.5	6.8

LOCKRINGS:



THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)	
		OUTSIDE DIAMETER	THICKNESS
1/2" IMP	WRES02	17.0	4.0
1.1/2" IMP	WRES07	45.0	5.0
2" IMP	WRES08	61.0	5.0
M16	WRMS03	21.0	4.5
M20	WRMS04	26.0	4.5
M25	WRMS05	32.0	4.5
M32	WRMS06	38.0	5.0
M20	*MXWR04	25.4	3.5
M25	*MXWR05	32.0	3.5
M32	*MXWR06	30.2	5.7

LOCKNUTS:



THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)	
		ACROSS FLATS	THICKNESS
M20	*MXWH04	28.0	3.5
M25	*MXWH05	28.0	4.0
M32	*MXWH06	38.0	5.0
M16	WHMB03	22.0	2.0
M20	WHMB04	27.0	2.0
M25	WHMB05	33.0	2.0
M32	WHMB06	41.0	4.3
M40	WHMB07	47.0	3.0
M50	WHMB08	64.0	3.0
M16	WHMM03	22.0	3.0
M20	WHMM04	24.0	3.5
M25	WHMM05	30.0	3.5
M32	WHMM06	35.0	4.5
M40	WHMM07	44.0	4.5
M50	WHMM08	55.0	7.0
M63	WHMM09	70.0	7.5
M16	WHMS03	23.2	3.5
M20	WHMS04	27.9	3.5
M25	WHMS05	34.5	3.5
M32	WHMS06	43.0	3.5
M40	WHMS07	49.5	4.0
M50	WHMS08	63.1	4.0
M63	WHMS09	78.0	5.0

THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)	
		ACROSS FLATS	THICKNESS
1/2" NPT	WHAM04	27.0	3.3
3/4" NPT	WHAM05	30.0	3.5
1" NPT	WHAM06	37.5	5.0
1.1/4" NPT	WHAM07	47.0	5.2
1.1/2" NPT	WHAM08	56.0	6.0
2" NPT	WHAM09	70.0	6.7
1/2" IMP	WHES02	17.0	4.0
1.1/2" IMP	WHES07	45.0	5.0
2" IMP	WHES08	61.0	5.0
2.1/2" IMP	WHEM09	79.0	5.0
3" IMP	WHEM10	88.0	5.0

LAST LETTER OF ORDERING CODE DENOTES: **S** – STEEL / SELF FINISH, ZINC PLATE OR BLACK ENAMEL; **B** – BRASS / SELF FINISH; **M** – BRASS / NICKEL PLATE. (PRE-FIX ***M** - STAINLESS STEEL).
 METRIC THREADS TO BS 6053. IMPERIAL THREADS TO BS 31. NPT THREADS TO ANSI B1.20.1

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.