


## Coaxial Cable Connector 16\_MCX-50-1-11/111\_N

### Description

Right angle cable plug

Interface standards

IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.000773 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00005780
Catalogue drawing	DOU-00005782
Assembly instruction	DOC-0000178655

### Ordering Information

Single package	16_MCX-50-1-11/111_NE
Bulk 100 pcs package	16_MCX-50-1-11/111_NH

### Additional Information

Suitable cables	EZ_47_TP_M17, SUCOFORM_47_CU
-----------------	------------------------------