## **Data Sheet**



# Coaxial Cable Connector 11\_PC35-50-3-4/199\_U

## **Description**

Straight cable plug

Interface standards IEC 60169-23



#### **Technical Data**

**Electrical Data** 

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 26.5 \ \text{GHz} \end{array}$ 

**Mechanical Data** 

Centre contact plugged
Outer contact soldered
Weight 0.0057 kg

**Environmental Data** 

Operating temperature -60 °C to 100 °C 2011/65/EU (RoHS - including compliant 2015/863 and 2017/2102)

#### **Material Data**

| Piece Parts    | Material               | Surface Plating                            |
|----------------|------------------------|--|
| Centre contact | Copper Beryllium Alloy | Gold Plating (without Nickel underplating) |
| Outer contact  | Stainless Steel        |  |
| Body           | Stainless Steel        |  |
| Insulator      | PS (Polystyrene)       |  |
| Coupling nut   | Stainless Steel        |  |
| Gasket         | VMQ (Silicone rubber)  |  |

### **Related Documents**

Outline drawing DOU-00064428
Catalogue drawing DCA-00089646
Assembly instruction DOC-0000215467

## **Ordering Information**

Single package 11\_PC35-50-3-4/199\_UE

#### **Additional Information**

Suitable cables EZ\_141\_TP\_M17, EZ\_141\_AL\_TP\_M17, SUCOFORM\_141, MULTIFLEX\_141

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.