Data Sheet



Coaxial Cable Connector 24_TNC-50-3-30/133_N

Description

Straight bulkhead cable feed through

Interface standards
IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

 $\begin{array}{ll} \mbox{Impedance} & \mbox{50} \ \Omega \\ \mbox{Interface frequency max.} & \mbox{11 GHz} \end{array}$

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0177 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00009411
Catalogue drawing	DCA-00009413
Assembly instruction	DOC-0000185934
Mounting hole	DOU-00008751

Ordering Information

Bulk 100 pcs package 24_TNC-50-3-30/133_NH

Additional Information

Suitable cables EZ_141_TP_M17

Remarks

El. Optimized for cable EZ 141

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.