



fitted with

work equipment
connected load
Power consumption
System of protection
class of protection
technology
usage
luminaire body
lamp cover
tubular sections
weight (net)
mains lead

LED

Energy efficiency category A+
 electronic plug-in transformer
 100-240 V; 50/60 Hz
 approx. 6 W
 IP 20
 II
 continuously dimmable
 Touch-LED
 aluminium/plastic, anodised, black
 Acrylic satine
 steel tube/metal flexible tube, painted, silver metallic
 approx. 1.1 kg
 approx. 2.3 m; mains plug
 BS 1363
 CEE 7/XVI
 NEMA 1-15P
 screw-down flange, magnetic base (accessory), table clamp (accessory), wall bracket (accessory)
 Ø 72 mm
 6
 not available

Fastening

lens; dimensions
lens; diopters
add-on lens; dimensions



BS 1363



CEE 7/XVI



NEMA 1-15P

illuminance

distance: 15 cm

Em: 2871 lx
Emax: 5587 lx
Emin: 888 lx

