EMI Shield Heat Shrink Tubing Kit







Description:

EMI Shield Heat Shrink Tubing (2:1) combines two proven technologies into a single, easy to install product for adding EMI protection to wire and cable bundles. It is ideal for cables diameters of 1/2" and less. The product is comprised of MIL-I-23053/5 polyolefin heat-shrink tubing and an EMI shielding fabric woven of nickel-over-copper-plated polyester taffeta cloth which provides outstanding shielding performance. This product is supplied in a one foot piece with three feet of 24AWG grounding wire and has a length tolerance of $\pm \frac{1}{2}$ inch.

Features:

- · Easy one-step installation
- · High performance Mil-Spec jacketing
- · Excellent high frequency EMI shielding
- · Government listed NSN's
- · Lower total installed costs

Specifications

Material : Polyolefin Heat-Shrink Tubing, 2:1 shrink ratio;

Nickel-over-Copper-Plated Polyester Taffeta Cloth Fabric Shield

Operating Temp. : -55°C to 135°C Thickness : 0.02" to 0.035"

Break Strength : 1,500 (after shrinkage)

Dielectric : 500V/mil (after shrinkage) Jacket, <0.1Ω/sq conductive shield

Flexibility : Medium
Fluid Resist : Excellent
Cable Types : Round

Size : 3/16, 1/4, 3/8, 1/2, 3/4, 1 (before shrinkage) N/A


Colour : Black







EMI Shield Heat Shrink Tubing Kit





Attenuation Levels (dB)				
10MHz	82			
50MHz	68			
100MHz	88			
300MHz	83			
500MHz	84			
700MHz	90			
1GHz	90			
2GHz	90			
5GHz	91			
10GHz	81			
20GHz	70			





Kit Includes

: 1ft of EMI Shield Heat Shrink Tubing and 3ft. 24AWG grounding wire

Part Number Table

Description	Nominal Size Before Shrinkage		Nominal Size After Shrinkage		
	A Inside Diameter (Inches)	B Wall Thickness (Inches)	C Inside Diameter (Inches)	D Wall Thickness (Inches)	Part Number
EMI Shield Heat Shrink Tubing Kit	0.187	0.01	0.093	0.02	SPC5086
	0.25		0.125	0.025	SPC5087
	0.375		0.188		SPC5088
	0.5		0.25		SPC5089
	0.75		0.375	0.03	SPC5090
	1		0.5	0.035	SPC5091

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

