Data Sheet



Between Series Adaptor 33_BNC-A-0-1/0--_-

Description

Adaptor plug/jack BNC plug (male) / A jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series A - SUHNER-A



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & \text{other } \Omega \\ \text{Interface frequency max.} & \text{4 GHz} \end{array}$

Mechanical Data

Number of matings 500
Weight 0.0192 kg

Environmental Data

Operating temperature -20 °C to 85 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - A jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Bronze	
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00014399

Ordering Information

Single package 33_BNC-A-0-1/0--_-E

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.